

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221167

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221167
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 1218 LIGHT ENGINE, BLACK SHADE, NARROW DISTRIBUTION.
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8291.1 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.95
Luminous Opening: Vertical Cylinder (Dia: 1.58' x H: 0.67')
CIE Type: Direct

Input Watts (W): 81.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221167

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)

Luminous Intensity Polar Plot



CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	91	94	92	89	92	89	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	88	85	82	86	83	81	79		
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	75	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51		
10	70	60	54	50	69	59	53	50	58	53	49	58	53	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44505
5°	42211
10°	39205
15°	35962
20°	32115
25°	27755
30°	22155
35°	15572
40°	9302
45°	3260
50°	2828
55°	410
60°	115
65°	107
70°	100
75°	85
80°	63
85°	35

MAXIMUM LUMINANCE 45°-90°:

Luminance: 3596 cd/sqm

TEST NUMBER: P1221167

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	758.2	9.1
10°-20°	2032.0	24.5
20°-30°	2613.2	31.5
30°-40°	1992.0	24.0
40°-50°	712.0	8.6
50°-60°	141.6	1.7
60°-70°	17.4	0.2
70°-80°	12.7	0.2
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.1	0.0
130°-140°	0.8	0.0
140°-150°	1.8	0.0
150°-160°	2.1	0.0
160°-170°	1.8	0.0
170°-180°	0.7	0.0
0°-30°	5403.4	65.2
0°-40°	7395.4	89.2
0°-60°	8249.0	99.5
0°-90°	8283.8	99.9
90°-120°	0.0	0.0
90°-150°	2.7	0.0
90°-180°	7.0	0.1
0°-180°	8291.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8141	
5°	8053	758
15°	7267	2032
25°	5752	2613
35°	3209	1992
45°	648	712
55°	76	142
65°	18	17
75°	12	13
85°	4	4
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	1	1
145°	3	2
155°	5	2
165°	6	2
175°	7	1
180°	7	

TEST NUMBER: P1221167

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8140.9
2.5°	8103.7
5°	8052.7
7.5°	7924.2
10°	7730.1
12.5°	7519.1
15°	7266.8
17.5°	6954.7
20°	6597.3
22.5°	6209.1
25°	5751.5
27.5°	5255.0
30°	4596.0
32.5°	3886.9
35°	3209.3
37.5°	2554.3
40°	1889.7
42.5°	1173.3
45°	647.7
47.5°	704.3
50°	545.0
52.5°	257.9
55°	76.0
57.5°	34.0
60°	20.2
62.5°	18.6
65°	17.8
67.5°	16.2
70°	15.4
72.5°	13.7
75°	12.1
77.5°	10.5
80°	8.1
82.5°	6.5
85°	4.0
87.5°	2.4
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P1221167

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.8
132.5°	0.8
135°	0.8
137.5°	1.6
140°	1.6
142.5°	2.4
145°	3.2
147.5°	3.2
150°	4.0
152.5°	4.0
155°	4.9
157.5°	4.9
160°	5.7
162.5°	5.7
165°	6.5
167.5°	6.5
170°	7.3
172.5°	7.3
175°	7.3
177.5°	7.3
180°	7.3

TEST NUMBER: P1221167

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (3000K_L12_Narrow_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT