

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503985

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (2700K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (2700K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, BRASS REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 837.4 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503985

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (2700K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503985

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (2700K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
R																				
C	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
R	1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89	
C	2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77	
R	3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67	
C	4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58	
R	5	81	69	61	55	79	68	61	55	66	60	54	64	58	54	63	57	53	51	
C	6	75	63	55	49	73	62	54	49	60	53	48	58	52	48	57	52	47	45	
R	7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40	
C	8	65	52	44	39	63	52	44	39	50	43	39	49	43	38	48	42	38	36	
R	9	61	48	40	35	59	47	40	35	46	40	35	45	39	35	44	39	35	33	
C	10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3723
5°	3712
10°	3706
15°	3691
20°	3667
25°	3628
30°	3589
35°	3544
40°	3491
45°	3390
50°	3073
55°	2605
60°	1951
65°	1141
70°	353
75°	187
80°	209
85°	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3390 cd/sqm

TEST NUMBER: P1503985

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (2700K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.9	4.2
10°-20°	99.9	11.9
20°-30°	150.6	18.0
30°-40°	180.2	21.5
40°-50°	181.8	21.7
50°-60°	131.8	15.7
60°-70°	49.5	5.9
70°-80°	6.2	0.7
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.4	34.1
0°-40°	465.7	55.6
0°-60°	779.3	93.1
0°-90°	837.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	837.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	370	
5°	367	35
15°	354	100
25°	327	151
35°	288	180
45°	238	182
55°	148	132
65°	48	49
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1503985

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (2700K-900LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	369.7
2.5°	368.5
5°	367.3
7.5°	364.9
10°	362.5
12.5°	360.1
15°	354.1
17.5°	348.2
20°	342.2
22.5°	335.0
25°	326.6
27.5°	318.2
30°	308.7
32.5°	297.9
35°	288.3
37.5°	277.6
40°	265.6
42.5°	254.8
45°	238.1
47.5°	218.9
50°	196.2
52.5°	173.5
55°	148.4
57.5°	123.2
60°	96.9
62.5°	71.8
65°	47.9
67.5°	27.5
70°	12.0
72.5°	6.0
75°	4.8
77.5°	4.8
80°	3.6
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)