

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503998

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (2700K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-24)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (2700K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1147.8 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503998

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (2700K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503998

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (2700K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	45			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5918
5°	5940
10°	5905
15°	5721
20°	5481
25°	5231
30°	4903
35°	4580
40°	4230
45°	3811
50°	3343
55°	2825
60°	2251
65°	1815
70°	1796
75°	1712
80°	1571
85°	1375

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3811 cd/sqm

TEST NUMBER: P1503998

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (2700K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.8	4.9
10°-20°	154.2	13.4
20°-30°	215.6	18.8
30°-40°	232.5	20.3
40°-50°	206.1	18.0
50°-60°	144.2	12.6
60°-70°	79.5	6.9
70°-80°	46.5	4.0
80°-90°	13.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.6	37.1
0°-40°	658.1	57.3
0°-60°	1008.4	87.9
0°-90°	1147.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1147.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	588	
5°	588	56
15°	549	154
25°	471	216
35°	373	232
45°	268	206
55°	161	144
65°	76	80
75°	44	46
85°	12	13
90°	0	

TEST NUMBER: P1503998

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (2700K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	587.7
2.5°	587.7
5°	587.7
7.5°	586.0
10°	577.5
12.5°	565.7
15°	548.8
17.5°	530.1
20°	511.5
22.5°	491.2
25°	470.8
27.5°	445.4
30°	421.7
32.5°	396.3
35°	372.6
37.5°	347.2
40°	321.8
42.5°	294.7
45°	267.6
47.5°	240.5
50°	213.4
52.5°	188.0
55°	160.9
57.5°	135.5
60°	111.8
62.5°	91.5
65°	76.2
67.5°	67.7
70°	61.0
72.5°	52.5
75°	44.0
77.5°	35.6
80°	27.1
82.5°	18.6
85°	11.9
87.5°	5.1
90°	0.0

(END OF REPORT)