

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504028

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504028
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-16)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1363.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504028

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504028

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	94	88	83	99	93	87	82	89	84	80	86	82	79	83	80	77	75		
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	61	55	51	49		
6	73	61	52	46	72	60	52	46	58	51	46	57	50	45	55	49	45	43		
7	68	55	47	41	66	55	47	41	53	46	41	52	45	40	50	45	40	38		
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34		
9	59	46	39	33	58	46	38	33	45	38	33	44	37	33	43	37	33	31		
10	56	43	35	30	54	42	35	30	41	35	30	40	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5628
5°	5615
10°	5611
15°	5597
20°	5572
25°	5551
30°	5494
35°	5454
40°	5432
45°	5306
50°	4934
55°	4341
60°	3480
65°	2461
70°	1345
75°	1120
80°	1177
85°	1178

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5306 cd/sqm

TEST NUMBER: P1504028

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	3.9
10°-20°	151.6	11.1
20°-30°	229.8	16.9
30°-40°	277.9	20.4
40°-50°	285.2	20.9
50°-60°	219.5	16.1
60°-70°	103.6	7.6
70°-80°	31.9	2.3
80°-90°	10.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.2	31.9
0°-40°	712.1	52.2
0°-60°	1216.8	89.3
0°-90°	1363.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1363.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	559	
5°	556	53
15°	537	152
25°	500	230
35°	444	278
45°	373	285
55°	247	219
65°	103	104
75°	29	32
85°	10	11
90°	0	

TEST NUMBER: P1504028

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	558.9
2.5°	557.2
5°	555.5
7.5°	552.1
10°	548.8
12.5°	543.7
15°	536.9
17.5°	530.1
20°	520.0
22.5°	509.8
25°	499.6
27.5°	486.1
30°	472.5
32.5°	459.0
35°	443.7
37.5°	428.5
40°	413.3
42.5°	396.3
45°	372.6
47.5°	345.5
50°	315.0
52.5°	282.8
55°	247.3
57.5°	210.0
60°	172.8
62.5°	137.2
65°	103.3
67.5°	71.1
70°	45.7
72.5°	33.9
75°	28.8
77.5°	25.4
80°	20.3
82.5°	15.2
85°	10.2
87.5°	3.4
90°	0.0

(END OF REPORT)