

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504089

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 733.2 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504089

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504089

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3779
5°	3804
10°	3781
15°	3661
20°	3516
25°	3341
30°	3139
35°	2927
40°	2697
45°	2438
50°	2132
55°	1792
60°	1436
65°	1151
70°	1130
75°	1066
80°	1021
85°	890

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2438 cd/sqm

TEST NUMBER: P1504089

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	4.9
10°-20°	98.8	13.5
20°-30°	138.2	18.8
30°-40°	148.7	20.3
40°-50°	131.7	18.0
50°-60°	91.9	12.5
60°-70°	50.5	6.9
70°-80°	29.1	4.0
80°-90°	8.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.7	37.2
0°-40°	421.4	57.5
0°-60°	645.0	88.0
0°-90°	733.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	733.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	375	
5°	376	36
15°	351	99
25°	301	138
35°	238	149
45°	171	132
55°	102	92
65°	48	50
75°	27	29
85°	8	9
90°	0	

TEST NUMBER: P1504089

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	375.3
2.5°	375.3
5°	376.4
7.5°	375.3
10°	369.8
12.5°	362.1
15°	351.2
17.5°	340.2
20°	328.1
22.5°	315.0
25°	300.7
27.5°	286.4
30°	270.0
32.5°	254.6
35°	238.1
37.5°	221.7
40°	205.2
42.5°	188.8
45°	171.2
47.5°	153.6
50°	136.1
52.5°	119.6
55°	102.1
57.5°	86.7
60°	71.3
62.5°	58.2
65°	48.3
67.5°	42.8
70°	38.4
72.5°	32.9
75°	27.4
77.5°	21.9
80°	17.6
82.5°	12.1
85°	7.7
87.5°	3.3
90°	0.0

(END OF REPORT)