

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504401

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3000K_L18_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504401
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3000K_L18_Wide_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12274.6 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.14
Luminous Opening: Circular (Dia: 1.29' x H: 0')
CIE Type: Direct

Input Watts (W): 122.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504401

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3000K_L18_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504401

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3000K_L18_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92							
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84							
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77							
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	74	71	70							
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64							
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58							
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53							
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49							
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45							
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68929
5°	68859
10°	68625
15°	68973
20°	68708
25°	68703
30°	68404
35°	58675
40°	42804
45°	27069
50°	11830
55°	2413
60°	849
65°	612
70°	701
75°	749
80°	743
85°	745

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27069 cd/sqm

TEST NUMBER: P1504401

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3000K_L18_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	792.9	6.5
10°-20°	2285.6	18.6
20°-30°	3492.6	28.5
30°-40°	3578.7	29.2
40°-50°	1809.9	14.7
50°-60°	246.8	2.0
60°-70°	35.0	0.3
70°-80°	24.6	0.2
80°-90°	8.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6571.1	53.5
0°-40°	10149.7	82.7
0°-60°	12206.4	99.4
0°-90°	12274.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12274.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8391	
5°	8351	793
15°	8110	2286
25°	7580	3493
35°	5851	3579
45°	2330	1810
55°	168	247
65°	32	35
75°	24	25
85°	8	9
90°	0	

TEST NUMBER: P1504401

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3000K_L18_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	8391.2
2.5°	8365.4
5°	8350.8
7.5°	8296.9
10°	8227.2
12.5°	8173.3
15°	8110.4
17.5°	7998.0
20°	7859.8
22.5°	7720.5
25°	7580.1
27.5°	7419.4
30°	7211.6
32.5°	6611.7
35°	5851.1
37.5°	4974.8
40°	3991.7
42.5°	3126.6
45°	2330.1
47.5°	1599.8
50°	925.7
52.5°	374.1
55°	168.5
57.5°	97.7
60°	51.7
62.5°	39.3
65°	31.5
67.5°	30.3
70°	29.2
72.5°	27.0
75°	23.6
77.5°	20.2
80°	15.7
82.5°	12.4
85°	7.9
87.5°	3.4
90°	0.0

(END OF REPORT)