

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504578

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3000K_L16_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504578
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3000K_L16_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13131.0 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.29
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 102.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504578

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3000K_L16_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504578

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3000K_L16_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	99	94	90	103	98	93	89	94	91	87	91	88	85	88	86	84	82		
3	98	90	84	80	96	89	83	79	86	81	78	84	80	76	81	78	75	73		
4	92	82	76	71	90	81	75	70	79	74	69	77	72	68	75	71	68	66		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	60	56	65	60	55	64	59	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62447
5°	62602
10°	62740
15°	63092
20°	62957
25°	62950
30°	62923
35°	62602
40°	57498
45°	44760
50°	28120
55°	13999
60°	3196
65°	1444
70°	587
75°	421
80°	483
85°	576

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44760 cd/sqm

TEST NUMBER: P1504578

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3000K_L16_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	685.6	5.2
10°-20°	1985.3	15.1
20°-30°	3039.0	23.1
30°-40°	3663.0	27.9
40°-50°	2777.0	21.1
50°-60°	880.4	6.7
60°-70°	80.2	0.6
70°-80°	14.5	0.1
80°-90°	6.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5709.9	43.5
0°-40°	9372.9	71.4
0°-60°	13030.3	99.2
0°-90°	13131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7215	
5°	7205	686
15°	7041	1985
25°	6592	3039
35°	5925	3663
45°	3657	2777
55°	928	880
65°	70	80
75°	13	15
85°	6	6
90°	0	

TEST NUMBER: P1504578

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3000K_L16_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	7214.8
2.5°	7200.3
5°	7205.2
7.5°	7184.9
10°	7138.5
12.5°	7094.0
15°	7040.9
17.5°	6952.9
20°	6835.0
22.5°	6712.3
25°	6591.5
27.5°	6455.3
30°	6295.8
32.5°	6122.8
35°	5924.7
37.5°	5668.6
40°	5088.8
42.5°	4411.4
45°	3656.7
47.5°	2852.7
50°	2088.3
52.5°	1455.3
55°	927.7
57.5°	479.3
60°	184.6
62.5°	116.0
65°	70.5
67.5°	36.7
70°	23.2
72.5°	14.5
75°	12.6
77.5°	11.6
80°	9.7
82.5°	8.7
85°	5.8
87.5°	2.9
90°	0.0

(END OF REPORT)