

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504754

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3000K_L12_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504754
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3000K_L12_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8957.9 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.96
Luminous Opening: Circular (Dia: 1.3' x H: 0')
CIE Type: Direct

Input Watts (W): 82.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504754

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3000K_L12_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504754

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3000K_L12_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93								
2	107	102	97	93	105	100	96	92	97	93	90	93	91	88	91	89	87	85								
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78								
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71								
5	90	80	74	69	88	79	74	69	78	72	68	76	71	68	74	70	67	66								
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60								
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56								
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52								
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48								
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65693
5°	65179
10°	63188
15°	60231
20°	55992
25°	50488
30°	43208
35°	33810
40°	25750
45°	16813
50°	8705
55°	4356
60°	1012
65°	357
70°	346
75°	357
80°	341
85°	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16813 cd/sqm

TEST NUMBER: P1504754

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3000K_L12_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	753.5	8.4
10°-20°	2006.1	22.4
20°-30°	2569.7	28.7
30°-40°	2146.4	24.0
40°-50°	1147.2	12.8
50°-60°	293.3	3.3
60°-70°	25.6	0.3
70°-80°	11.7	0.1
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5329.4	59.5
0°-40°	7475.8	83.5
0°-60°	8916.3	99.5
0°-90°	8957.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8957.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8101	
5°	8007	754
15°	7174	2006
25°	5642	2570
35°	3415	2146
45°	1466	1147
55°	308	293
65°	19	26
75°	11	12
85°	4	4
90°	0	

TEST NUMBER: P1504754

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	8100.8
2.5°	8056.3
5°	8006.8
7.5°	7876.3
10°	7673.5
12.5°	7445.7
15°	7174.1
17.5°	6849.8
20°	6488.1
22.5°	6088.4
25°	5642.5
27.5°	5144.6
30°	4614.3
32.5°	3991.6
35°	3415.2
37.5°	2906.8
40°	2432.4
42.5°	1935.4
45°	1466.0
47.5°	1058.1
50°	690.0
52.5°	499.5
55°	308.1
57.5°	149.2
60°	62.4
62.5°	30.8
65°	18.6
67.5°	16.2
70°	14.6
72.5°	13.0
75°	11.4
77.5°	8.9
80°	7.3
82.5°	5.7
85°	4.1
87.5°	2.4
90°	0.0

(END OF REPORT)