

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504151

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-21)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, BRASS REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 993.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.22
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504151

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504151

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85		
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73		
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	65	62		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48		
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	54	49	44	42		
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38		
8	64	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34		
9	60	47	39	34	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	36	31	55	43	35	31	42	35	30	41	35	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4481
5°	4479
10°	4492
15°	4462
20°	4404
25°	4232
30°	3990
35°	3732
40°	3470
45°	3168
50°	2806
55°	2482
60°	2165
65°	2156
70°	2220
75°	2202
80°	2076
85°	1964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3168 cd/sqm

TEST NUMBER: P1504151

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	4.2
10°-20°	120.6	12.1
20°-30°	174.7	17.6
30°-40°	190.0	19.1
40°-50°	171.2	17.2
50°-60°	126.7	12.8
60°-70°	89.9	9.1
70°-80°	59.4	6.0
80°-90°	18.2	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.5	34.0
0°-40°	527.6	53.1
0°-60°	825.5	83.1
0°-90°	993.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	993.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	445	
5°	443	42
15°	428	121
25°	381	175
35°	304	190
45°	222	171
55°	141	127
65°	90	90
75°	57	59
85°	17	18
90°	0	

TEST NUMBER: P1504151

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-1200LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	445.0
2.5°	445.0
5°	443.1
7.5°	441.2
10°	439.3
12.5°	433.7
15°	428.0
17.5°	420.5
20°	411.0
22.5°	396.0
25°	380.9
27.5°	363.9
30°	343.2
32.5°	324.3
35°	303.6
37.5°	284.7
40°	264.0
42.5°	243.2
45°	222.5
47.5°	201.7
50°	179.1
52.5°	160.3
55°	141.4
57.5°	122.6
60°	107.5
62.5°	98.0
65°	90.5
67.5°	83.0
70°	75.4
72.5°	66.0
75°	56.6
77.5°	47.1
80°	35.8
82.5°	26.4
85°	17.0
87.5°	5.7
90°	0.0

(END OF REPORT)