

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504153

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-21)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, BRASS REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 701.4 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.22
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504153

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504153

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85							
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73							
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	65	62							
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54							
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48							
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	54	49	44	42							
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38							
8	64	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34							
9	60	47	39	34	58	46	39	33	45	38	33	44	38	33	43	37	33	31							
10	56	43	36	31	55	43	35	31	42	35	30	41	35	30	40	34	30	28							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3165
5°	3164
10°	3173
15°	3151
20°	3112
25°	2989
30°	2818
35°	2635
40°	2451
45°	2238
50°	1982
55°	1754
60°	1528
65°	1522
70°	1569
75°	1556
80°	1467
85°	1386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2238 cd/sqm

TEST NUMBER: P1504153

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.8	4.2
10°-20°	85.2	12.1
20°-30°	123.4	17.6
30°-40°	134.2	19.1
40°-50°	121.0	17.2
50°-60°	89.5	12.8
60°-70°	63.5	9.1
70°-80°	42.0	6.0
80°-90°	12.9	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	238.4	34.0
0°-40°	372.6	53.1
0°-60°	583.1	83.1
0°-90°	701.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	701.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	314	
5°	313	30
15°	302	85
25°	269	123
35°	214	134
45°	157	121
55°	100	89
65°	64	63
75°	40	42
85°	12	13
90°	0	

TEST NUMBER: P1504153

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3000K-900LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	314.3
2.5°	314.3
5°	313.0
7.5°	311.7
10°	310.3
12.5°	306.3
15°	302.3
17.5°	297.0
20°	290.4
22.5°	279.7
25°	269.0
27.5°	257.1
30°	242.4
32.5°	229.1
35°	214.4
37.5°	201.1
40°	186.5
42.5°	171.8
45°	157.2
47.5°	142.5
50°	126.5
52.5°	113.2
55°	99.9
57.5°	86.6
60°	75.9
62.5°	69.3
65°	63.9
67.5°	58.6
70°	53.3
72.5°	46.6
75°	40.0
77.5°	33.3
80°	25.3
82.5°	18.6
85°	12.0
87.5°	4.0
90°	0.0

(END OF REPORT)