

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504198

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHITE-XX-OT (3000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 784.5 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.24
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504198

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504198

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47			
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34			
9	59	46	38	33	58	45	38	33	44	37	33	43	37	32	42	36	32	30			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3406
5°	3419
10°	3418
15°	3401
20°	3354
25°	3241
30°	3081
35°	2914
40°	2731
45°	2503
50°	2253
55°	2010
60°	1796
65°	1808
70°	1843
75°	1813
80°	1774
85°	1537

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2503 cd/sqm

TEST NUMBER: P1504198

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.1	4.1
10°-20°	92.0	11.7
20°-30°	134.1	17.1
30°-40°	148.1	18.9
40°-50°	135.5	17.3
50°-60°	103.0	13.1
60°-70°	75.2	9.6
70°-80°	49.2	6.3
80°-90°	15.4	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.2	32.9
0°-40°	406.3	51.8
0°-60°	644.8	82.2
0°-90°	784.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	338	
5°	338	32
15°	326	92
25°	292	134
35°	237	148
45°	176	135
55°	114	103
65°	76	75
75°	47	49
85°	13	15
90°	0	

TEST NUMBER: P1504198

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	338.3
2.5°	338.3
5°	338.3
7.5°	335.6
10°	334.3
12.5°	331.6
15°	326.3
17.5°	321.0
20°	313.0
22.5°	303.7
25°	291.7
27.5°	279.7
30°	265.0
32.5°	251.7
35°	237.1
37.5°	222.4
40°	207.8
42.5°	191.8
45°	175.8
47.5°	159.8
50°	143.8
52.5°	129.2
55°	114.5
57.5°	101.2
60°	89.2
62.5°	82.6
65°	75.9
67.5°	69.3
70°	62.6
72.5°	54.6
75°	46.6
77.5°	38.6
80°	30.6
82.5°	22.6
85°	13.3
87.5°	5.3
90°	0.0

(END OF REPORT)