

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503959

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (3500K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (3500K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1136.1 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503959

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (3500K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503959

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (3500K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	64	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5855
5°	5895
10°	5859
15°	5672
20°	5448
25°	5176
30°	4863
35°	4536
40°	4180
45°	3778
50°	3302
55°	2775
60°	2225
65°	1782
70°	1752
75°	1653
80°	1577
85°	1375

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3778 cd/sqm

TEST NUMBER: P1503959

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (3500K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.4	4.9
10°-20°	153.0	13.5
20°-30°	214.1	18.8
30°-40°	230.4	20.3
40°-50°	204.1	18.0
50°-60°	142.3	12.5
60°-70°	78.2	6.9
70°-80°	45.1	4.0
80°-90°	13.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.6	37.2
0°-40°	653.0	57.5
0°-60°	999.4	88.0
0°-90°	1136.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1136.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	582	
5°	583	55
15°	544	153
25°	466	214
35°	369	230
45°	265	204
55°	158	142
65°	75	78
75°	42	45
85°	12	13
90°	0	

TEST NUMBER: P1503959

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (3500K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	581.5
2.5°	581.5
5°	583.2
7.5°	581.5
10°	573.0
12.5°	561.1
15°	544.1
17.5°	527.1
20°	508.4
22.5°	488.0
25°	465.9
27.5°	443.8
30°	418.3
32.5°	394.5
35°	369.0
37.5°	343.5
40°	318.0
42.5°	292.5
45°	265.3
47.5°	238.1
50°	210.8
52.5°	185.3
55°	158.1
57.5°	134.3
60°	110.5
62.5°	90.1
65°	74.8
67.5°	66.3
70°	59.5
72.5°	51.0
75°	42.5
77.5°	34.0
80°	27.2
82.5°	18.7
85°	11.9
87.5°	5.1
90°	0.0

(END OF REPORT)