

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504141

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3500K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-24)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3500K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 912.2 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504141

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3500K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504141

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3500K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	45		
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4703
5°	4721
10°	4693
15°	4546
20°	4356
25°	4157
30°	3897
35°	3640
40°	3362
45°	3029
50°	2657
55°	2245
60°	1788
65°	1444
70°	1428
75°	1362
80°	1247
85°	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3029 cd/sqm

TEST NUMBER: P1504141

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3500K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	4.9
10°-20°	122.5	13.4
20°-30°	171.4	18.8
30°-40°	184.8	20.3
40°-50°	163.8	18.0
50°-60°	114.6	12.6
60°-70°	63.2	6.9
70°-80°	36.9	4.0
80°-90°	10.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.3	37.1
0°-40°	523.0	57.3
0°-60°	801.4	87.9
0°-90°	912.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	912.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	467	44
15°	436	123
25°	374	171
35°	296	185
45°	213	164
55°	128	115
65°	61	63
75°	35	37
85°	9	11
90°	0	

TEST NUMBER: P1504141

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3500K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	467.1
2.5°	467.1
5°	467.1
7.5°	465.8
10°	459.0
12.5°	449.6
15°	436.1
17.5°	421.3
20°	406.5
22.5°	390.4
25°	374.2
27.5°	354.0
30°	335.2
32.5°	315.0
35°	296.1
37.5°	276.0
40°	255.8
42.5°	234.2
45°	212.7
47.5°	191.1
50°	169.6
52.5°	149.4
55°	127.9
57.5°	107.7
60°	88.8
62.5°	72.7
65°	60.6
67.5°	53.8
70°	48.5
72.5°	41.7
75°	35.0
77.5°	28.3
80°	21.5
82.5°	14.8
85°	9.4
87.5°	4.0
90°	0.0

(END OF REPORT)