

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504068

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 596.1 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.24
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504068

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504068

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47			
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34			
9	59	46	38	33	58	45	38	33	44	37	33	43	37	32	42	36	32	30			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2588
5°	2598
10°	2597
15°	2584
20°	2548
25°	2462
30°	2342
35°	2214
40°	2075
45°	1902
50°	1712
55°	1527
60°	1365
65°	1375
70°	1401
75°	1377
80°	1351
85°	1167

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1902 cd/sqm

TEST NUMBER: P1504068

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	4.1
10°-20°	69.9	11.7
20°-30°	101.8	17.1
30°-40°	112.5	18.9
40°-50°	102.9	17.3
50°-60°	78.3	13.1
60°-70°	57.1	9.6
70°-80°	37.4	6.3
80°-90°	11.7	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.1	32.9
0°-40°	308.7	51.8
0°-60°	489.9	82.2
0°-90°	596.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	257	
5°	257	24
15°	248	70
25°	222	102
35°	180	113
45°	134	103
55°	87	78
65°	58	57
75°	35	37
85°	10	12
90°	0	

TEST NUMBER: P1504068

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	257.0
2.5°	257.0
5°	257.0
7.5°	255.0
10°	254.0
12.5°	252.0
15°	247.9
17.5°	243.9
20°	237.8
22.5°	230.7
25°	221.6
27.5°	212.5
30°	201.4
32.5°	191.2
35°	180.1
37.5°	169.0
40°	157.9
42.5°	145.7
45°	133.6
47.5°	121.4
50°	109.3
52.5°	98.2
55°	87.0
57.5°	76.9
60°	67.8
62.5°	62.7
65°	57.7
67.5°	52.6
70°	47.6
72.5°	41.5
75°	35.4
77.5°	29.3
80°	23.3
82.5°	17.2
85°	10.1
87.5°	4.0
90°	0.0

(END OF REPORT)