

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504099

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 905.7 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504099

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504099

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4668
5°	4700
10°	4670
15°	4522
20°	4343
25°	4126
30°	3877
35°	3616
40°	3332
45°	3012
50°	2633
55°	2214
60°	1774
65°	1420
70°	1395
75°	1319
80°	1258
85°	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3012 cd/sqm

TEST NUMBER: P1504099

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	4.9
10°-20°	122.0	13.5
20°-30°	170.7	18.8
30°-40°	183.7	20.3
40°-50°	162.8	18.0
50°-60°	113.5	12.5
60°-70°	62.3	6.9
70°-80°	35.9	4.0
80°-90°	10.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.9	37.2
0°-40°	520.6	57.5
0°-60°	796.8	88.0
0°-90°	905.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	905.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	464	
5°	465	44
15°	434	122
25°	371	171
35°	294	184
45°	212	163
55°	126	113
65°	60	62
75°	34	36
85°	10	11
90°	0	

TEST NUMBER: P1504099

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-900LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	463.6
2.5°	463.6
5°	465.0
7.5°	463.6
10°	456.8
12.5°	447.3
15°	433.8
17.5°	420.2
20°	405.3
22.5°	389.0
25°	371.4
27.5°	353.8
30°	333.5
32.5°	314.5
35°	294.2
37.5°	273.8
40°	253.5
42.5°	233.2
45°	211.5
47.5°	189.8
50°	168.1
52.5°	147.8
55°	126.1
57.5°	107.1
60°	88.1
62.5°	71.8
65°	59.6
67.5°	52.9
70°	47.4
72.5°	40.7
75°	33.9
77.5°	27.1
80°	21.7
82.5°	14.9
85°	9.5
87.5°	4.1
90°	0.0

(END OF REPORT)