

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504202

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (4000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHITE-XX-OT (4000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1130.6 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.24
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504202

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (4000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504202

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (4000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47			
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34			
9	59	46	38	33	58	45	38	33	44	37	33	43	37	32	42	36	32	30			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4909
5°	4927
10°	4925
15°	4901
20°	4833
25°	4669
30°	4440
35°	4199
40°	3935
45°	3607
50°	3247
55°	2897
60°	2590
65°	2606
70°	2655
75°	2614
80°	2557
85°	2218

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3607 cd/sqm

TEST NUMBER: P1504202

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (4000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.3	4.1
10°-20°	132.6	11.7
20°-30°	193.2	17.1
30°-40°	213.4	18.9
40°-50°	195.2	17.3
50°-60°	148.5	13.1
60°-70°	108.3	9.6
70°-80°	70.9	6.3
80°-90°	22.2	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.0	32.9
0°-40°	585.4	51.8
0°-60°	929.1	82.2
0°-90°	1130.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1130.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	488	
5°	488	46
15°	470	133
25°	420	193
35°	342	213
45°	253	195
55°	165	148
65°	109	108
75°	67	71
85°	19	22
90°	0	

TEST NUMBER: P1504202

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (4000K-1200LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	487.5
2.5°	487.5
5°	487.5
7.5°	483.6
10°	481.7
12.5°	477.9
15°	470.2
17.5°	462.5
20°	451.0
22.5°	437.6
25°	420.3
27.5°	403.0
30°	381.9
32.5°	362.7
35°	341.6
37.5°	320.5
40°	299.4
42.5°	276.4
45°	253.3
47.5°	230.3
50°	207.3
52.5°	186.2
55°	165.0
57.5°	145.9
60°	128.6
62.5°	119.0
65°	109.4
67.5°	99.8
70°	90.2
72.5°	78.7
75°	67.2
77.5°	55.7
80°	44.1
82.5°	32.6
85°	19.2
87.5°	7.7
90°	0.0

(END OF REPORT)