

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504070

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (5000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (5000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1033.1 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.24
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504070

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (5000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504070

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (5000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85		
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62		
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54		
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47		
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37		
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34		
9	59	46	38	33	58	45	38	33	44	37	33	43	37	32	42	36	32	30		
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4486
5°	4503
10°	4501
15°	4479
20°	4417
25°	4267
30°	4058
35°	3838
40°	3596
45°	3296
50°	2967
55°	2647
60°	2366
65°	2383
70°	2426
75°	2389
80°	2337
85°	2022

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3296 cd/sqm

TEST NUMBER: P1504070

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (5000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.3	4.1
10°-20°	121.2	11.7
20°-30°	176.5	17.1
30°-40°	195.1	18.9
40°-50°	178.4	17.3
50°-60°	135.7	13.1
60°-70°	99.0	9.6
70°-80°	64.8	6.3
80°-90°	20.3	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.0	32.9
0°-40°	535.0	51.8
0°-60°	849.1	82.2
0°-90°	1033.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	446	
5°	446	42
15°	430	121
25°	384	177
35°	312	195
45°	232	178
55°	151	136
65°	100	99
75°	61	65
85°	18	20
90°	0	

TEST NUMBER: P1504070

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (5000K-1200LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	445.5
2.5°	445.5
5°	445.5
7.5°	442.0
10°	440.2
12.5°	436.7
15°	429.7
17.5°	422.7
20°	412.2
22.5°	399.9
25°	384.1
27.5°	368.3
30°	349.0
32.5°	331.5
35°	312.2
37.5°	292.9
40°	273.6
42.5°	252.6
45°	231.5
47.5°	210.5
50°	189.4
52.5°	170.1
55°	150.8
57.5°	133.3
60°	117.5
62.5°	108.7
65°	100.0
67.5°	91.2
70°	82.4
72.5°	71.9
75°	61.4
77.5°	50.9
80°	40.3
82.5°	29.8
85°	17.5
87.5°	7.0
90°	0.0

(END OF REPORT)