

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504100

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (5000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (5000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1300.1 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 13.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504100

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (5000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504100

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (5000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46		
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34		
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6701
5°	6746
10°	6705
15°	6491
20°	6234
25°	5924
30°	5566
35°	5191
40°	4783
45°	4323
50°	3780
55°	3177
60°	2547
65°	2039
70°	2005
75°	1891
80°	1803
85°	1571

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4323 cd/sqm

TEST NUMBER: P1504100

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (5000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.4	4.9
10°-20°	175.1	13.5
20°-30°	245.1	18.8
30°-40°	263.7	20.3
40°-50°	233.6	18.0
50°-60°	162.9	12.5
60°-70°	89.4	6.9
70°-80°	51.6	4.0
80°-90°	15.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.6	37.2
0°-40°	747.3	57.5
0°-60°	1143.8	88.0
0°-90°	1300.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1300.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	667	63
15°	623	175
25°	533	245
35°	422	264
45°	304	234
55°	181	163
65°	86	89
75°	49	52
85°	14	15
90°	0	

TEST NUMBER: P1504100

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (5000K-1200LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	665.5
2.5°	665.5
5°	667.4
7.5°	665.5
10°	655.8
12.5°	642.1
15°	622.7
17.5°	603.2
20°	581.8
22.5°	558.5
25°	533.2
27.5°	507.9
30°	478.7
32.5°	451.5
35°	422.3
37.5°	393.1
40°	363.9
42.5°	334.7
45°	303.6
47.5°	272.4
50°	241.3
52.5°	212.1
55°	181.0
57.5°	153.7
60°	126.5
62.5°	103.1
65°	85.6
67.5°	75.9
70°	68.1
72.5°	58.4
75°	48.6
77.5°	38.9
80°	31.1
82.5°	21.4
85°	13.6
87.5°	5.8
90°	0.0

(END OF REPORT)