

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504117

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (5000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504117
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-20)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (5000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 704.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.22
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504117

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (5000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504117

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (5000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85		
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73		
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	65	62		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48		
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	55	49	44	43		
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38		
8	64	51	43	37	62	50	42	37	49	42	37	47	41	36	46	41	36	34		
9	60	47	39	34	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	36	31	55	43	36	31	42	35	30	41	35	30	40	34	30	29		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3183
5°	3182
10°	3190
15°	3180
20°	3122
25°	3009
30°	2829
35°	2653
40°	2457
45°	2231
50°	2002
55°	1738
60°	1522
65°	1539
70°	1578
75°	1603
80°	1513
85°	1271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2231 cd/sqm

TEST NUMBER: P1504117

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (5000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.0	4.3
10°-20°	85.9	12.2
20°-30°	124.1	17.6
30°-40°	134.5	19.1
40°-50°	120.9	17.2
50°-60°	89.3	12.7
60°-70°	63.6	9.0
70°-80°	42.4	6.0
80°-90°	13.3	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	240.0	34.1
0°-40°	374.6	53.2
0°-60°	584.7	83.1
0°-90°	704.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	316	
5°	315	30
15°	305	86
25°	271	124
35°	216	135
45°	157	121
55°	99	89
65°	65	64
75°	41	42
85°	11	13
90°	0	

TEST NUMBER: P1504117

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (5000K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	316.1
2.5°	316.1
5°	314.8
7.5°	314.8
10°	312.0
12.5°	309.3
15°	305.1
17.5°	299.6
20°	291.4
22.5°	281.8
25°	270.8
27.5°	258.4
30°	243.3
32.5°	229.5
35°	215.8
37.5°	200.7
40°	186.9
42.5°	171.8
45°	156.7
47.5°	141.6
50°	127.8
52.5°	112.7
55°	99.0
57.5°	86.6
60°	75.6
62.5°	68.7
65°	64.6
67.5°	59.1
70°	53.6
72.5°	46.7
75°	41.2
77.5°	33.0
80°	26.1
82.5°	19.2
85°	11.0
87.5°	5.5
90°	0.0

(END OF REPORT)