

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504145

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (5000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-24)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (5000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1318.7 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 13.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504145

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (5000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504145

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (5000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	45			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6799
5°	6825
10°	6785
15°	6572
20°	6297
25°	6010
30°	5633
35°	5262
40°	4859
45°	4379
50°	3841
55°	3246
60°	2586
65°	2087
70°	2064
75°	1969
80°	1803
85°	1571

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4379 cd/sqm

TEST NUMBER: P1504145

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (5000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	4.9
10°-20°	177.1	13.4
20°-30°	247.8	18.8
30°-40°	267.1	20.3
40°-50°	236.8	18.0
50°-60°	165.7	12.6
60°-70°	91.4	6.9
70°-80°	53.4	4.0
80°-90°	15.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.0	37.1
0°-40°	756.1	57.3
0°-60°	1158.6	87.9
0°-90°	1318.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1318.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	675	
5°	675	64
15°	630	177
25°	541	248
35°	428	267
45°	308	237
55°	185	166
65°	88	91
75°	51	53
85°	14	15
90°	0	

TEST NUMBER: P1504145

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (5000K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	675.2
2.5°	675.2
5°	675.2
7.5°	673.3
10°	663.6
12.5°	649.9
15°	630.5
17.5°	609.1
20°	587.7
22.5°	564.3
25°	541.0
27.5°	511.8
30°	484.5
32.5°	455.3
35°	428.1
37.5°	398.9
40°	369.7
42.5°	338.6
45°	307.5
47.5°	276.3
50°	245.2
52.5°	216.0
55°	184.9
57.5°	155.7
60°	128.4
62.5°	105.1
65°	87.6
67.5°	77.8
70°	70.1
72.5°	60.3
75°	50.6
77.5°	40.9
80°	31.1
82.5°	21.4
85°	13.6
87.5°	5.8
90°	0.0

(END OF REPORT)