

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504191

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (5000K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-22)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (5000K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 827.2 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.19
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504191

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (5000K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504191

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (5000K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87		
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75		
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50		
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40		
8	65	52	45	39	64	52	44	39	50	44	39	49	43	39	48	43	38	37		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	44	37	32	43	37	32	43	37	32	42	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4176
5°	4192
10°	4171
15°	4048
20°	3866
25°	3702
30°	3500
35°	3262
40°	3035
45°	2748
50°	2430
55°	2057
60°	1665
65°	1396
70°	1354
75°	1295
80°	1200
85°	1063

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2748 cd/sqm

TEST NUMBER: P1504191

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (5000K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	4.8
10°-20°	109.0	13.2
20°-30°	153.0	18.5
30°-40°	166.0	20.1
40°-50°	148.7	18.0
50°-60°	105.4	12.7
60°-70°	60.2	7.3
70°-80°	34.9	4.2
80°-90°	10.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	301.4	36.4
0°-40°	467.4	56.5
0°-60°	721.5	87.2
0°-90°	827.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	827.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	415	
5°	415	39
15°	388	109
25°	333	153
35°	265	166
45°	193	149
55°	117	105
65°	59	60
75°	33	35
85°	9	11
90°	0	

TEST NUMBER: P1504191

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (5000K-750LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	414.7
2.5°	414.7
5°	414.7
7.5°	413.6
10°	407.9
12.5°	399.8
15°	388.3
17.5°	375.7
20°	360.8
22.5°	348.1
25°	333.2
27.5°	317.1
30°	301.0
32.5°	282.6
35°	265.4
37.5°	248.2
40°	230.9
42.5°	211.4
45°	193.0
47.5°	174.6
50°	155.1
52.5°	136.7
55°	117.2
57.5°	100.0
60°	82.7
62.5°	68.9
65°	58.6
67.5°	51.7
70°	46.0
72.5°	39.1
75°	33.3
77.5°	26.4
80°	20.7
82.5°	14.9
85°	9.2
87.5°	4.6
90°	0.0

(END OF REPORT)