

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504354

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504354
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-23)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE
SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16594.1 lumens
Efficiency: N/A
Efficacy: 135.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.14
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 122.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504354

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504354

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91586
5°	91709
10°	91592
15°	91248
20°	89046
25°	85804
30°	80803
35°	72512
40°	59751
45°	47058
50°	37687
55°	21520
60°	11780
65°	9275
70°	8670
75°	9990
80°	11818
85°	13539

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 47058 cd/sqm

TEST NUMBER: P1504354

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	951.0	5.7
10°-20°	2711.0	16.3
20°-30°	3902.9	23.5
30°-40°	4010.1	24.2
40°-50°	2853.0	17.2
50°-60°	1292.2	7.8
60°-70°	444.4	2.7
70°-80°	295.1	1.8
80°-90°	134.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7564.9	45.6
0°-40°	11575.0	69.8
0°-60°	15720.2	94.7
0°-90°	16594.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16594.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10028	
5°	10003	951
15°	9651	2711
25°	8515	3903
35°	6504	4010
45°	3643	2853
55°	1352	1292
65°	429	444
75°	283	295
85°	129	134
90°	0	

TEST NUMBER: P1504354

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	10028.2
2.5°	10001.2
5°	10003.4
7.5°	9966.4
10°	9876.5
12.5°	9786.6
15°	9650.7
17.5°	9441.7
20°	9162.0
22.5°	8848.5
25°	8514.8
27.5°	8126.1
30°	7662.1
32.5°	7121.7
35°	6503.8
37.5°	5779.2
40°	5011.8
42.5°	4284.9
45°	3643.4
47.5°	3104.2
50°	2652.5
52.5°	2030.1
55°	1351.5
57.5°	814.5
60°	644.9
62.5°	524.7
65°	429.2
67.5°	360.6
70°	324.7
72.5°	300.0
75°	283.1
77.5°	259.5
80°	224.7
82.5°	182.0
85°	129.2
87.5°	69.7
90°	0.0

(END OF REPORT)