

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504356

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504356
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-24)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17377.9 lumens
Efficiency: N/A
Efficacy: 141.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.31 / 1.3
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 122.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504356

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Wide_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1504356

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	65	72	67	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50		
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41		
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	47	40	36	46	40	36	45	40	36	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79417
5°	79494
10°	79663
15°	80380
20°	80550
25°	80857
30°	81170
35°	81193
40°	74927
45°	59436
50°	39827
55°	23453
60°	11471
65°	10513
70°	11071
75°	13201
80°	16252
85°	19899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 59436 cd/sqm

TEST NUMBER: P1504356

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	825.1	4.7
10°-20°	2398.1	13.8
20°-30°	3700.3	21.3
30°-40°	4493.9	25.9
40°-50°	3508.3	20.2
50°-60°	1377.8	7.9
60°-70°	493.0	2.8
70°-80°	390.1	2.2
80°-90°	191.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6923.5	39.8
0°-40°	11417.4	65.7
0°-60°	16303.5	93.8
0°-90°	17377.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	17377.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8696	
5°	8671	825
15°	8501	2398
25°	8024	3700
35°	7282	4494
45°	4602	3508
55°	1473	1378
65°	486	493
75°	374	390
85°	190	191
90°	0	

TEST NUMBER: P1504356

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3000K_L18_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8695.7
2.5°	8672.1
5°	8671.0
7.5°	8644.0
10°	8590.1
12.5°	8548.5
15°	8501.3
17.5°	8410.3
20°	8287.9
22.5°	8155.3
25°	8023.9
27.5°	7873.3
30°	7696.9
32.5°	7501.5
35°	7282.4
37.5°	6940.8
40°	6284.7
42.5°	5489.3
45°	4601.8
47.5°	3678.3
50°	2803.1
52.5°	2082.9
55°	1472.9
57.5°	956.1
60°	628.0
62.5°	546.0
65°	486.5
67.5°	438.2
70°	414.6
72.5°	392.1
75°	374.1
77.5°	348.3
80°	309.0
82.5°	259.5
85°	189.9
87.5°	98.9
90°	0.0

(END OF REPORT)