

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504213

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L12_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504213
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L12_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10700.4 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 82.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504213

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L12_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504213

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91								
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83								
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75								
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67								
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61								
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	56								
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51								
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	46								
9	68	56	50	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43								
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65706
5°	65740
10°	65411
15°	64704
20°	62467
25°	59702
30°	55546
35°	48842
40°	39343
45°	30391
50°	24032
55°	11722
60°	4280
65°	1804
70°	521
75°	258
80°	300
85°	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30391 cd/sqm

TEST NUMBER: P1504213

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	680.8	6.4
10°-20°	1919.2	17.9
20°-30°	2713.1	25.4
30°-40°	2702.2	25.3
40°-50°	1851.7	17.3
50°-60°	723.2	6.8
60°-70°	97.5	0.9
70°-80°	9.3	0.1
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5313.0	49.7
0°-40°	8015.2	74.9
0°-60°	10590.1	99.0
0°-90°	10700.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10700.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7194	
5°	7171	681
15°	6843	1919
25°	5925	2713
35°	4381	2702
45°	2353	1852
55°	736	723
65°	84	98
75°	7	9
85°	3	3
90°	0	

TEST NUMBER: P1504213

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	7194.4
2.5°	7173.3
5°	7170.8
7.5°	7132.7
10°	7053.3
12.5°	6965.7
15°	6843.3
17.5°	6658.4
20°	6427.3
22.5°	6183.3
25°	5924.6
27.5°	5624.6
30°	5267.1
32.5°	4847.0
35°	4380.8
37.5°	3848.9
40°	3300.0
42.5°	2794.1
45°	2353.0
47.5°	2008.4
50°	1691.4
52.5°	1235.7
55°	736.2
57.5°	350.3
60°	234.3
62.5°	147.6
65°	83.5
67.5°	40.5
70°	19.5
72.5°	8.9
75°	7.3
77.5°	6.5
80°	5.7
82.5°	4.9
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)