

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504715

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3000K_L18_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504715
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3000K_L18_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16080.1 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 122.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504715

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3000K_L18_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504715

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3000K_L18_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	67	62	83	74	67	62	72	66	61	70	65	60	68	64	60	58		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	55	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99906
5°	99234
10°	96392
15°	92236
20°	86212
25°	78336
30°	67899
35°	56815
40°	47806
45°	41242
50°	37760
55°	23277
60°	13089
65°	9480
70°	8217
75°	9093
80°	10248
85°	10596

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 41943 cd/sqm

TEST NUMBER: P1504715

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3000K_L18_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1075.7	6.7
10°-20°	2880.3	17.9
20°-30°	3738.5	23.2
30°-40°	3381.4	21.0
40°-50°	2680.8	16.7
50°-60°	1438.1	8.9
60°-70°	487.1	3.0
70°-80°	283.6	1.8
80°-90°	114.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7694.6	47.9
0°-40°	11075.9	68.9
0°-60°	15194.9	94.5
0°-90°	16080.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16080.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11543	
5°	11421	###
15°	10293	2880
25°	8202	3739
35°	5377	3381
45°	3369	2681
55°	1542	1438
65°	463	487
75°	272	284
85°	107	114
90°	0	

TEST NUMBER: P1504715

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3000K_L18_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	11542.6
2.5°	11488.7
5°	11421.3
7.5°	11248.2
10°	10967.4
12.5°	10656.2
15°	10293.3
17.5°	9857.4
20°	9359.7
22.5°	8812.5
25°	8202.5
27.5°	7517.2
30°	6793.7
32.5°	6074.6
35°	5377.0
37.5°	4768.0
40°	4231.0
42.5°	3753.5
45°	3369.3
47.5°	3273.8
50°	2804.2
52.5°	2216.6
55°	1542.5
57.5°	958.3
60°	756.1
62.5°	594.3
65°	462.9
67.5°	376.4
70°	324.7
72.5°	293.2
75°	271.9
77.5°	243.8
80°	205.6
82.5°	158.4
85°	106.7
87.5°	52.8
90°	0.0

(END OF REPORT)