

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504219

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L18_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504219
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L18_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14826.6 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 122.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504219

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L18_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504219

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L18_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91								
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83								
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75								
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67								
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61								
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	56								
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51								
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	46								
9	68	56	50	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43								
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91042
5°	91091
10°	90634
15°	89654
20°	86556
25°	82724
30°	76964
35°	67677
40°	54514
45°	42110
50°	33298
55°	16243
60°	5931
65°	2500
70°	721
75°	356
80°	415
85°	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42110 cd/sqm

TEST NUMBER: P1504219

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L18_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	943.3	6.4
10°-20°	2659.2	17.9
20°-30°	3759.3	25.4
30°-40°	3744.2	25.3
40°-50°	2565.7	17.3
50°-60°	1002.1	6.8
60°-70°	135.2	0.9
70°-80°	12.9	0.1
80°-90°	4.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7361.8	49.7
0°-40°	11106.0	74.9
0°-60°	14673.8	99.0
0°-90°	14826.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14826.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9969	
5°	9936	943
15°	9482	2659
25°	8209	3759
35°	6070	3744
45°	3260	2566
55°	1020	1002
65°	116	135
75°	10	13
85°	4	5
90°	0	

TEST NUMBER: P1504219

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (3000K_L18_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	9968.6
2.5°	9939.4
5°	9936.0
7.5°	9883.2
10°	9773.1
12.5°	9651.8
15°	9482.1
17.5°	9226.0
20°	8905.8
22.5°	8567.6
25°	8209.2
27.5°	7793.6
30°	7298.1
32.5°	6716.1
35°	6070.1
37.5°	5333.1
40°	4572.5
42.5°	3871.5
45°	3260.3
47.5°	2782.9
50°	2343.6
52.5°	1712.2
55°	1020.1
57.5°	485.3
60°	324.7
62.5°	204.5
65°	115.7
67.5°	56.2
70°	27.0
72.5°	12.4
75°	10.1
77.5°	9.0
80°	7.9
82.5°	6.7
85°	4.5
87.5°	2.2
90°	0.0

(END OF REPORT)