

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504582

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L12_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504582
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-29)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L12_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11077.6 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.12
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 81.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504582

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L12_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504582

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91							
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83							
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74							
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67							
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61							
6	81	71	64	59	80	70	63	58	68	62	58	67	61	57	65	61	57	55							
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50							
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46							
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43							
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63876
5°	63953
10°	63660
15°	62947
20°	60904
25°	58226
30°	54094
35°	47763
40°	38857
45°	30114
50°	23765
55°	12191
60°	4257
65°	1843
70°	549
75°	278
80°	289
85°	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30114 cd/sqm

TEST NUMBER: P1504582

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	698.9	6.3
10°-20°	1971.4	17.8
20°-30°	2791.8	25.2
30°-40°	2793.4	25.2
40°-50°	1932.3	17.4
50°-60°	771.8	7.0
60°-70°	104.0	0.9
70°-80°	10.4	0.1
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5462.2	49.3
0°-40°	8255.5	74.5
0°-60°	10959.7	98.9
0°-90°	11077.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11077.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7380	
5°	7361	699
15°	7025	1971
25°	6097	2792
35°	4520	2793
45°	2460	1932
55°	808	772
65°	90	104
75°	8	10
85°	3	4
90°	0	

TEST NUMBER: P1504582

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	7379.9
2.5°	7363.2
5°	7360.7
7.5°	7324.0
10°	7243.2
12.5°	7150.6
15°	7024.7
17.5°	6843.0
20°	6612.1
22.5°	6366.1
25°	6096.8
27.5°	5789.2
30°	5412.4
32.5°	4988.0
35°	4520.3
37.5°	4005.9
40°	3439.0
42.5°	2922.9
45°	2460.2
47.5°	2086.7
50°	1764.9
52.5°	1312.2
55°	807.9
57.5°	379.3
60°	245.9
62.5°	156.7
65°	90.0
67.5°	44.2
70°	21.7
72.5°	10.0
75°	8.3
77.5°	7.5
80°	5.8
82.5°	5.0
85°	3.3
87.5°	1.7
90°	0.0

(END OF REPORT)