

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504585

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504585
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-29)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13287.4 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.12
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 100.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504585

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504585

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	71	64	59	80	70	63	58	68	62	58	67	61	57	65	61	57	55		
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50		
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43		
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76618
5°	76711
10°	76359
15°	75503
20°	73052
25°	69841
30°	64884
35°	57291
40°	46608
45°	36122
50°	28506
55°	14623
60°	5107
65°	2212
70°	658
75°	334
80°	349
85°	397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36122 cd/sqm

TEST NUMBER: P1504585

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	838.4	6.3
10°-20°	2364.7	17.8
20°-30°	3348.7	25.2
30°-40°	3350.6	25.2
40°-50°	2317.8	17.4
50°-60°	925.8	7.0
60°-70°	124.7	0.9
70°-80°	12.5	0.1
80°-90°	4.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6551.7	49.3
0°-40°	9902.3	74.5
0°-60°	13145.9	98.9
0°-90°	13287.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13287.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8852	
5°	8829	838
15°	8426	2365
25°	7313	3349
35°	5422	3351
45°	2951	2318
55°	969	926
65°	108	125
75°	10	13
85°	4	4
90°	0	

TEST NUMBER: P1504585

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8852
2.5°	8832
5°	8829
7.5°	8785
10°	8688
12.5°	8577
15°	8426
17.5°	8208
20°	7931
22.5°	7636
25°	7313
27.5°	6944
30°	6492
32.5°	5983
35°	5422
37.5°	4805
40°	4125
42.5°	3506
45°	2951
47.5°	2503
50°	2117
52.5°	1574
55°	969
57.5°	455
60°	295
62.5°	188
65°	108
67.5°	53
70°	26
72.5°	12
75°	10
77.5°	9
80°	7
82.5°	6
85°	4
87.5°	2
90°	0

(END OF REPORT)