

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504587

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504587
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13588.2 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.29
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 100.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504587

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504587

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	99	94	90	103	98	93	89	94	91	87	91	88	85	88	86	84	82		
3	98	90	84	80	96	89	83	79	86	81	78	84	80	76	81	78	75	73		
4	92	82	76	71	90	81	75	70	79	74	69	77	72	68	75	71	68	66		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	60	56	65	60	55	64	59	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64622
5°	64781
10°	64924
15°	65288
20°	65149
25°	65142
30°	65114
35°	64782
40°	59500
45°	46319
50°	29099
55°	14487
60°	3306
65°	1495
70°	607
75°	435
80°	498
85°	596

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 46319 cd/sqm

TEST NUMBER: P1504587

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	709.5	5.2
10°-20°	2054.4	15.1
20°-30°	3144.8	23.1
30°-40°	3790.6	27.9
40°-50°	2873.7	21.1
50°-60°	911.0	6.7
60°-70°	82.9	0.6
70°-80°	15.0	0.1
80°-90°	6.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5908.7	43.5
0°-40°	9699.3	71.4
0°-60°	13484.0	99.2
0°-90°	13588.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13588.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7466	
5°	7456	709
15°	7286	2054
25°	6821	3145
35°	6131	3791
45°	3784	2874
55°	960	911
65°	73	83
75°	13	15
85°	6	6
90°	0	

TEST NUMBER: P1504587

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L16_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7466
2.5°	7451
5°	7456
7.5°	7435
10°	7387
12.5°	7341
15°	7286
17.5°	7195
20°	7073
22.5°	6946
25°	6821
27.5°	6680
30°	6515
32.5°	6336
35°	6131
37.5°	5866
40°	5266
42.5°	4565
45°	3784
47.5°	2952
50°	2161
52.5°	1506
55°	960
57.5°	496
60°	191
62.5°	120
65°	73
67.5°	38
70°	24
72.5°	15
75°	13
77.5°	12
80°	10
82.5°	9
85°	6
87.5°	3
90°	0

(END OF REPORT)