

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504769

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3500K_L18_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504769
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3500K_L18_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12873.4 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.96
Luminous Opening: Circular (Dia: 1.3' x H: 0')
CIE Type: Direct

Input Watts (W): 120.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504769

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3500K_L18_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504769

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3500K_L18_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93								
2	107	102	97	93	105	100	96	92	97	93	90	93	91	88	91	89	87	85								
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78								
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71								
5	90	80	74	69	88	79	74	69	78	72	68	76	71	68	74	70	67	66								
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60								
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56								
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52								
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48								
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94408
5°	93668
10°	90808
15°	86557
20°	80466
25°	72555
30°	62096
35°	48588
40°	37006
45°	24161
50°	12510
55°	6261
60°	1455
65°	514
70°	498
75°	511
80°	490
85°	540

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24161 cd/sqm

TEST NUMBER: P1504769

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3500K_L18_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1082.9	8.4
10°-20°	2883.0	22.4
20°-30°	3692.9	28.7
30°-40°	3084.6	24.0
40°-50°	1648.6	12.8
50°-60°	421.6	3.3
60°-70°	36.8	0.3
70°-80°	16.7	0.1
80°-90°	6.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7658.8	59.5
0°-40°	10743.4	83.5
0°-60°	12813.6	99.5
0°-90°	12873.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12873.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11642	
5°	11506	###
15°	10310	2883
25°	8109	3693
35°	4908	3085
45°	2107	1649
55°	443	422
65°	27	37
75°	16	17
85°	6	6
90°	0	

TEST NUMBER: P1504769

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (3500K_L18_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	11641.7
2.5°	11577.6
5°	11506.5
7.5°	11318.9
10°	11027.6
12.5°	10700.2
15°	10309.8
17.5°	9843.8
20°	9324.1
22.5°	8749.6
25°	8108.7
27.5°	7393.3
30°	6631.3
32.5°	5736.4
35°	4907.9
37.5°	4177.3
40°	3495.7
42.5°	2781.4
45°	2106.7
47.5°	1520.6
50°	991.6
52.5°	717.8
55°	442.8
57.5°	214.4
60°	89.7
62.5°	44.3
65°	26.8
67.5°	23.3
70°	21.0
72.5°	18.6
75°	16.3
77.5°	12.8
80°	10.5
82.5°	8.2
85°	5.8
87.5°	3.5
90°	0.0

(END OF REPORT)