

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504532

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (3000K_L16_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504532
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-46)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (3000K_L16_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13185.6 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.98
Luminous Opening: Circular (Dia: 1.29' x H: 0')
CIE Type: Direct

Input Watts (W): 102.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504532

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (3000K_L16_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504532

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (3000K_L16_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59		
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	50		
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46		
9	67	56	49	44	66	56	49	44	54	48	44	54	48	44	53	48	44	42		
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83469
5°	82776
10°	80235
15°	76856
20°	72041
25°	65567
30°	56619
35°	45372
40°	35854
45°	24282
50°	17302
55°	12856
60°	9747
65°	10142
70°	11187
75°	11870
80°	12205
85°	12573

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24282 cd/sqm

TEST NUMBER: P1504532

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (3000K_L16_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	944.8	7.2
10°-20°	2530.2	19.2
20°-30°	3295.5	25.0
30°-40°	2844.5	21.6
40°-50°	1692.5	12.8
50°-60°	824.4	6.3
60°-70°	520.3	3.9
70°-80°	390.1	3.0
80°-90°	143.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6770.6	51.3
0°-40°	9615.1	72.9
0°-60°	12131.9	92.0
0°-90°	13185.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13185.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10161	
5°	10038	945
15°	9037	2530
25°	7234	3295
35°	4524	2845
45°	2090	1692
55°	898	824
65°	522	520
75°	374	390
85°	133	143
90°	0	

TEST NUMBER: P1504532

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-WHGL-PS (3000K_L16_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	10161.2
2.5°	10113.9
5°	10038.5
7.5°	9873.3
10°	9619.1
12.5°	9348.5
15°	9037.4
17.5°	8667.3
20°	8241.1
22.5°	7770.5
25°	7234.1
27.5°	6635.0
30°	5969.2
32.5°	5214.5
35°	4524.5
37.5°	3920.5
40°	3343.6
42.5°	2714.5
45°	2090.2
47.5°	1697.9
50°	1353.9
52.5°	1136.4
55°	897.7
57.5°	698.7
60°	593.3
62.5°	549.9
65°	521.8
67.5°	498.6
70°	465.8
72.5°	424.2
75°	374.0
77.5°	317.9
80°	258.0
82.5°	197.1
85°	133.4
87.5°	66.7
90°	0.0

(END OF REPORT)