

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504891

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (3000K_L16_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504891
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (3000K_L16_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13839.5 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.09
Luminous Opening: Circular (Dia: 1.3' x H: 0')
CIE Type: Direct

Input Watts (W): 102.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504891

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (3000K_L16_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504891

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (3000K_L16_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	82	77	95	87	81	77	85	80	75	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	85	75	67	62	83	73	67	62	72	66	61	70	65	60	68	63	60	58		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	55	53		
7	75	64	56	51	73	63	56	51	61	55	51	60	55	50	59	54	50	48		
8	70	59	52	47	69	58	52	47	57	51	47	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	44	40	62	51	44	40	50	44	40	49	44	40	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72803
5°	72978
10°	72899
15°	72296
20°	70419
25°	68111
30°	64275
35°	53057
40°	39509
45°	26366
50°	16044
55°	12569
60°	10580
65°	11106
70°	12121
75°	12627
80°	12726
85°	12319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26366 cd/sqm

TEST NUMBER: P1504891

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (3000K_L16_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	852.2	6.2
10°-20°	2419.4	17.5
20°-30°	3488.0	25.2
30°-40°	3315.6	24.0
40°-50°	1809.3	13.1
50°-60°	812.8	5.9
60°-70°	575.2	4.2
70°-80°	420.9	3.0
80°-90°	146.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6759.6	48.8
0°-40°	10075.2	72.8
0°-60°	12697.3	91.7
0°-90°	13839.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13839.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8978	
5°	8965	852
15°	8611	2419
25°	7612	3488
35°	5359	3316
45°	2299	1809
55°	889	813
65°	579	575
75°	403	421
85°	132	146
90°	0	

TEST NUMBER: P1504891

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (3000K_L16_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	8977.5
2.5°	8957.2
5°	8964.9
7.5°	8933.0
10°	8852.8
12.5°	8755.2
15°	8611.2
17.5°	8408.3
20°	8159.9
22.5°	7895.1
25°	7612.0
27.5°	7272.8
30°	6864.0
32.5°	6160.5
35°	5359.4
37.5°	4540.9
40°	3732.1
42.5°	2997.6
45°	2299.0
47.5°	1684.4
50°	1271.7
52.5°	1048.5
55°	889.0
57.5°	748.0
60°	652.3
62.5°	610.7
65°	578.8
67.5°	549.9
70°	511.2
72.5°	460.0
75°	403.0
77.5°	340.2
80°	272.5
82.5°	203.9
85°	132.4
87.5°	64.7
90°	0.0

(END OF REPORT)