

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504408

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3500K_L18_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504408
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3500K_L18_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12777.9 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.05
Luminous Opening: Circular (Dia: 1.29' x H: 0')
CIE Type: Direct

Input Watts (W): 120.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504408

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3500K_L18_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504408

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3500K_L18_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93								
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85								
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78								
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71								
5	90	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	66								
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60								
7	80	70	63	58	78	69	63	58	68	62	58	66	61	58	65	61	57	56								
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	56	53	52								
9	71	61	54	50	70	60	54	50	59	54	50	58	53	49	57	53	49	48								
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83637
5°	83601
10°	83139
15°	82307
20°	79776
25°	76568
30°	70978
35°	55468
40°	37859
45°	21225
50°	9128
55°	4322
60°	1053
65°	521
70°	588
75°	628
80°	662
85°	660

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21225 cd/sqm

TEST NUMBER: P1504408

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3500K_L18_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	962.2	7.5
10°-20°	2716.4	21.3
20°-30°	3865.4	30.3
30°-40°	3424.5	26.8
40°-50°	1457.1	11.4
50°-60°	290.2	2.3
60°-70°	33.3	0.3
70°-80°	20.8	0.2
80°-90°	7.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7544.1	59.0
0°-40°	10968.5	85.8
0°-60°	12715.9	99.5
0°-90°	12777.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12777.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10182	
5°	10139	962
15°	9678	2716
25°	8448	3865
35°	5531	3424
45°	1827	1457
55°	302	290
65°	27	33
75°	20	21
85°	7	8
90°	0	

TEST NUMBER: P1504408

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-06-BLAK-PS (3500K_L18_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	10181.7
2.5°	10151.4
5°	10138.6
7.5°	10075.6
10°	9967.3
12.5°	9848.4
15°	9678.3
17.5°	9428.9
20°	9126.0
22.5°	8805.5
25°	8447.8
27.5°	8034.2
30°	7483.0
32.5°	6570.7
35°	5531.3
37.5°	4509.4
40°	3530.6
42.5°	2661.4
45°	1827.1
47.5°	1076.7
50°	714.3
52.5°	480.1
55°	301.8
57.5°	148.0
60°	64.1
62.5°	38.5
65°	26.8
67.5°	25.6
70°	24.5
72.5°	22.1
75°	19.8
77.5°	17.5
80°	14.0
82.5°	11.7
85°	7.0
87.5°	3.5
90°	0.0

(END OF REPORT)