

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504590

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L18_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504590
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L18_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15833.2 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.29
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 120.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504590

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L18_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504590

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L18_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	99	94	90	103	98	93	89	94	91	87	91	88	85	88	86	84	82		
3	98	90	84	80	96	89	83	79	86	81	78	84	80	76	81	78	75	73		
4	92	82	76	71	90	81	75	70	79	74	69	77	72	68	75	71	68	66		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	60	56	65	60	55	64	59	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75298
5°	75485
10°	75651
15°	76075
20°	75913
25°	75904
30°	75872
35°	75485
40°	69330
45°	53971
50°	33906
55°	16880
60°	3853
65°	1743
70°	709
75°	505
80°	583
85°	695

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 53971 cd/sqm

TEST NUMBER: P1504590

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L18_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	826.7	5.2
10°-20°	2393.8	15.1
20°-30°	3664.4	23.1
30°-40°	4416.8	27.9
40°-50°	3348.4	21.1
50°-60°	1061.5	6.7
60°-70°	96.7	0.6
70°-80°	17.5	0.1
80°-90°	7.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6885.0	43.5
0°-40°	11301.8	71.4
0°-60°	15711.7	99.2
0°-90°	15833.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15833.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8700	
5°	8688	827
15°	8490	2394
25°	7948	3664
35°	7144	4417
45°	4409	3348
55°	1119	1062
65°	85	97
75°	15	18
85°	7	7
90°	0	

TEST NUMBER: P1504590

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (3500K_L18_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	8699.5
2.5°	8682.0
5°	8687.9
7.5°	8663.4
10°	8607.5
12.5°	8553.9
15°	8489.8
17.5°	8383.7
20°	8241.6
22.5°	8093.6
25°	7947.9
27.5°	7783.7
30°	7591.4
32.5°	7382.8
35°	7143.9
37.5°	6835.2
40°	6136.0
42.5°	5319.2
45°	4409.2
47.5°	3439.7
50°	2518.0
52.5°	1754.8
55°	1118.6
57.5°	577.9
60°	222.6
62.5°	139.8
65°	85.1
67.5°	44.3
70°	28.0
72.5°	17.5
75°	15.1
77.5°	14.0
80°	11.7
82.5°	10.5
85°	7.0
87.5°	3.5
90°	0.0

(END OF REPORT)