

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221184

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221184
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 1218 LIGHT ENGINE, BLACK SHADE, MEDIUM DISTRIBUTION.
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8767.2 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.02
Luminous Opening: Vertical Cylinder (Dia: 1.58' x H: 0.67')
CIE Type: Direct

Input Watts (W): 80.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221184

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1221184

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		86
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	84	80	76		82	78	75		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	69		67
6	86	76	70	65	84	75	69	65	74	69	65		72	68	64		62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		58
8	77	67	60	56	75	66	60	56	65	59	55		64	59	55		54
9	73	62	56	52	71	62	56	52	61	55	52		60	55	51		50
10	69	59	53	48	68	58	52	48	57	52	48		57	52	48		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40018
5°	38322
10°	36707
15°	35203
20°	32906
25°	30372
30°	26328
35°	18292
40°	10270
45°	3980
50°	1853
55°	358
60°	140
65°	128
70°	121
75°	108
80°	86
85°	53

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3980 cd/sqm

TEST NUMBER: P1221184

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	695.4	7.9
10°-20°	1996.5	22.8
20°-30°	2870.0	32.7
30°-40°	2325.3	26.5
40°-50°	722.4	8.2
50°-60°	105.4	1.2
60°-70°	21.2	0.2
70°-80°	16.1	0.2
80°-90°	6.5	0.1
90°-100°	0.1	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.5	0.0
130°-140°	1.2	0.0
140°-150°	2.1	0.0
150°-160°	2.3	0.0
160°-170°	1.8	0.0
170°-180°	0.7	0.0
0°-30°	5561.9	63.4
0°-40°	7887.2	90.0
0°-60°	8715.0	99.4
0°-90°	8758.8	99.9
90°-120°	0.1	0.0
90°-150°	3.9	0.0
90°-180°	9.0	0.1
0°-180°	8767.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7320	
5°	7311	695
15°	7114	1996
25°	6294	2870
35°	3770	2325
45°	791	722
55°	66	105
65°	21	21
75°	15	16
85°	6	6
90°	1	1
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	2	1
145°	3	2
155°	5	2
165°	6	2
175°	8	1
180°	8	

TEST NUMBER: P1221184

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7320.1
2.5°	7305.6
5°	7310.7
7.5°	7286.1
10°	7237.6
12.5°	7194.3
15°	7113.5
17.5°	6962.2
20°	6759.8
22.5°	6542.2
25°	6293.9
27.5°	5997.2
30°	5461.6
32.5°	4672.6
35°	3769.7
37.5°	2860.9
40°	2086.4
42.5°	1391.8
45°	790.7
47.5°	425.9
50°	357.1
52.5°	190.4
55°	66.3
57.5°	34.9
60°	24.7
62.5°	22.1
65°	21.3
67.5°	20.4
70°	18.7
72.5°	17.0
75°	15.3
77.5°	13.6
80°	11.1
82.5°	8.5
85°	6.0
87.5°	3.4
90°	0.9
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P1221184

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.9
130°	0.9
132.5°	0.9
135°	1.7
137.5°	1.7
140°	2.6
142.5°	2.6
145°	3.4
147.5°	4.3
150°	4.3
152.5°	4.3
155°	5.1
157.5°	5.1
160°	6.0
162.5°	6.0
165°	6.0
167.5°	6.8
170°	6.8
172.5°	6.8
175°	7.7
177.5°	7.7
180°	7.7

TEST NUMBER: P1221184

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L12_Medium_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT