

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221190

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221190
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 1218 LIGHT ENGINE, BLACK SHADE, MEDIUM DISTRIBUTION.
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12320.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.02
Luminous Opening: Vertical Cylinder (Dia: 1.58' x H: 0.67')
CIE Type: Direct

Input Watts (W): 118.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221190

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1221190

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74
5	91	82	76	71	89	81	75	71	79	74	70	77	73	69	76	72	69
6	86	76	70	65	84	75	69	65	74	69	65	72	68	64	71	67	64
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51
10	69	59	53	48	68	58	52	48	57	52	48	57	52	48	56	51	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56236
5°	53852
10°	51584
15°	49470
20°	46241
25°	42681
30°	36997
35°	25705
40°	14431
45°	5592
50°	2604
55°	503
60°	196
65°	180
70°	170
75°	151
80°	121
85°	74

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5592 cd/sqm

TEST NUMBER: P1221190

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	977.2	7.9
10°-20°	2805.6	22.8
20°-30°	4033.1	32.7
30°-40°	3267.7	26.5
40°-50°	1015.1	8.2
50°-60°	148.1	1.2
60°-70°	29.8	0.2
70°-80°	22.5	0.2
80°-90°	9.1	0.1
90°-100°	0.2	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.7	0.0
130°-140°	1.6	0.0
140°-150°	3.0	0.0
150°-160°	3.2	0.0
160°-170°	2.5	0.0
170°-180°	1.0	0.0
0°-30°	7815.9	63.4
0°-40°	11083.6	90.0
0°-60°	12246.9	99.4
0°-90°	12308.3	99.9
90°-120°	0.2	0.0
90°-150°	5.4	0.0
90°-180°	12.0	0.1
0°-180°	12320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10287	
5°	10274	977
15°	9996	2806
25°	8845	4033
35°	5297	3268
45°	1111	1015
55°	93	148
65°	30	30
75°	22	23
85°	8	8
90°	1	1
95°	0	0
105°	0	0
115°	0	0
125°	0	1
135°	2	2
145°	5	3
155°	7	3
165°	8	2
175°	11	1
180°	11	

TEST NUMBER: P1221190

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	10286.7
2.5°	10266.3
5°	10273.5
7.5°	10238.9
10°	10170.8
12.5°	10109.8
15°	9996.3
17.5°	9783.7
20°	9499.3
22.5°	9193.5
25°	8844.6
27.5°	8427.6
30°	7675.0
32.5°	6566.3
35°	5297.4
37.5°	4020.3
40°	2931.9
42.5°	1955.8
45°	1111.1
47.5°	598.6
50°	501.8
52.5°	267.6
55°	93.2
57.5°	49.0
60°	34.6
62.5°	31.1
65°	29.9
67.5°	28.7
70°	26.3
72.5°	23.9
75°	21.5
77.5°	19.1
80°	15.5
82.5°	11.9
85°	8.4
87.5°	4.8
90°	1.2
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P1221190

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	1.2
130°	1.2
132.5°	1.2
135°	2.4
137.5°	2.4
140°	3.6
142.5°	3.6
145°	4.8
147.5°	6.0
150°	6.0
152.5°	6.0
155°	7.2
157.5°	7.2
160°	8.4
162.5°	8.4
165°	8.4
167.5°	9.6
170°	9.6
172.5°	9.6
175°	10.8
177.5°	10.8
180°	10.8

TEST NUMBER: P1221190

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (4000K_L18_Medium_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.02	0.00	0.00	0.00	0.00	0.02
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT