

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504357

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L12_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504357
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-23)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L12_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE
SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12313.9 lumens
Efficiency: N/A
Efficacy: 150.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.14
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 81.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504357

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L12_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1504357

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67963
5°	68054
10°	67968
15°	67712
20°	66078
25°	63673
30°	59961
35°	53809
40°	44340
45°	34921
50°	27968
55°	15969
60°	8740
65°	6883
70°	6433
75°	7414
80°	8767
85°	10049

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34921 cd/sqm

TEST NUMBER: P1504357

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	705.7	5.7
10°-20°	2011.7	16.3
20°-30°	2896.3	23.5
30°-40°	2975.8	24.2
40°-50°	2117.1	17.2
50°-60°	958.9	7.8
60°-70°	329.8	2.7
70°-80°	219.0	1.8
80°-90°	99.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5613.7	45.6
0°-40°	8589.5	69.8
0°-60°	11665.5	94.7
0°-90°	12313.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12313.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7442	
5°	7423	706
15°	7162	2012
25°	6319	2896
35°	4826	2976
45°	2704	2117
55°	1003	959
65°	318	330
75°	210	219
85°	96	100
90°	0	

TEST NUMBER: P1504357

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7441.6
2.5°	7421.6
5°	7423.2
7.5°	7395.7
10°	7329.0
12.5°	7262.3
15°	7161.5
17.5°	7006.4
20°	6798.8
22.5°	6566.2
25°	6318.6
27.5°	6030.1
30°	5685.8
32.5°	5284.8
35°	4826.3
37.5°	4288.5
40°	3719.1
42.5°	3179.7
45°	2703.7
47.5°	2303.5
50°	1968.4
52.5°	1506.5
55°	1002.9
57.5°	604.4
60°	478.5
62.5°	389.3
65°	318.5
67.5°	267.6
70°	240.9
72.5°	222.6
75°	210.1
77.5°	192.6
80°	166.7
82.5°	135.1
85°	95.9
87.5°	51.7
90°	0.0

(END OF REPORT)