

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504362

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L16_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504362
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-24)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L16_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE
SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 2 - 16,000 LUMENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15467.9 lumens
Efficiency: N/A
Efficacy: 154.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.31 / 1.3
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 100.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504362

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L16_Wide_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1504362

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L16_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	65	72	67	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50		
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41		
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	47	40	36	46	40	36	45	40	36	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70689
5°	70757
10°	70907
15°	71546
20°	71697
25°	71970
30°	72249
35°	72269
40°	66692
45°	52903
50°	35450
55°	20875
60°	10211
65°	9357
70°	9853
75°	11750
80°	14463
85°	17709

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 52903 cd/sqm

TEST NUMBER: P1504362

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L16_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	734.4	4.7
10°-20°	2134.6	13.8
20°-30°	3293.6	21.3
30°-40°	4000.0	25.9
40°-50°	3122.7	20.2
50°-60°	1226.4	7.9
60°-70°	438.8	2.8
70°-80°	347.2	2.2
80°-90°	170.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6162.6	39.8
0°-40°	10162.6	65.7
0°-60°	14511.7	93.8
0°-90°	15467.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15467.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7740	
5°	7718	734
15°	7567	2135
25°	7142	3294
35°	6482	4000
45°	4096	3123
55°	1311	1226
65°	433	439
75°	333	347
85°	169	170
90°	0	

TEST NUMBER: P1504362

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (3500K_L16_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7740
2.5°	7719
5°	7718
7.5°	7694
10°	7646
12.5°	7609
15°	7567
17.5°	7486
20°	7377
22.5°	7259
25°	7142
27.5°	7008
30°	6851
32.5°	6677
35°	6482
37.5°	6178
40°	5594
42.5°	4886
45°	4096
47.5°	3274
50°	2495
52.5°	1854
55°	1311
57.5°	851
60°	559
62.5°	486
65°	433
67.5°	390
70°	369
72.5°	349
75°	333
77.5°	310
80°	275
82.5°	231
85°	169
87.5°	88
90°	0

(END OF REPORT)