

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504717

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3500K_L12_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504717
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3500K_L12_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12359.1 lumens
Efficiency: N/A
Efficacy: 151.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.13
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 81.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504717

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3500K_L12_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1504717

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3500K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	85	74	67	62	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65637
5°	65677
10°	65323
15°	64621
20°	62715
25°	60320
30°	56784
35°	50873
40°	41711
45°	33115
50°	27066
55°	15688
60°	8500
65°	6625
70°	6096
75°	6886
80°	7811
85°	8441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33115 cd/sqm

TEST NUMBER: P1504717

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3500K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	717.5	5.8
10°-20°	2025.0	16.4
20°-30°	2896.3	23.4
30°-40°	2968.9	24.0
40°-50°	2126.1	17.2
50°-60°	986.6	8.0
60°-70°	334.8	2.7
70°-80°	214.1	1.7
80°-90°	89.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5638.8	45.6
0°-40°	8607.7	69.6
0°-60°	11720.3	94.8
0°-90°	12359.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12359.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7583	
5°	7559	718
15°	7212	2025
25°	6316	2896
35°	4815	2969
45°	2705	2126
55°	1040	987
65°	324	335
75°	206	214
85°	85	90
90°	0	

TEST NUMBER: P1504717

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (3500K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7583.3
2.5°	7563.3
5°	7559.1
7.5°	7516.6
10°	7432.4
12.5°	7335.7
15°	7211.5
17.5°	7032.2
20°	6808.8
22.5°	6571.2
25°	6316.1
27.5°	6026.8
30°	5681.6
32.5°	5281.5
35°	4814.6
37.5°	4276.9
40°	3691.6
42.5°	3163.0
45°	2705.3
47.5°	2352.7
50°	2010.0
52.5°	1545.7
55°	1039.6
57.5°	626.1
60°	491.0
62.5°	396.8
65°	323.5
67.5°	269.3
70°	240.9
72.5°	220.9
75°	205.9
77.5°	185.1
80°	156.7
82.5°	122.6
85°	85.0
87.5°	44.2
90°	0.0

(END OF REPORT)