

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504727

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (4000K_L12_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504727
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (4000K_L12_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12092.0 lumens
Efficiency: N/A
Efficacy: 149.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 80.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504727

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (4000K_L12_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504727

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (4000K_L12_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	67	62	83	74	67	62	72	66	61	70	65	60	68	64	60	58		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	55	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75127
5°	74622
10°	72485
15°	69360
20°	64829
25°	58907
30°	51059
35°	42724
40°	35949
45°	31014
50°	28395
55°	17505
60°	9843
65°	7129
70°	6180
75°	6836
80°	7706
85°	7975

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 31540 cd/sqm

TEST NUMBER: P1504727

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (4000K_L12_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	808.9	6.7
10°-20°	2165.9	17.9
20°-30°	2811.3	23.2
30°-40°	2542.7	21.0
40°-50°	2015.9	16.7
50°-60°	1081.5	8.9
60°-70°	366.3	3.0
70°-80°	213.3	1.8
80°-90°	86.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5786.2	47.9
0°-40°	8328.9	68.9
0°-60°	11426.3	94.5
0°-90°	12092.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12092.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8680	
5°	8589	809
15°	7740	2166
25°	6168	2811
35°	4043	2543
45°	2534	2016
55°	1160	1081
65°	348	366
75°	204	213
85°	80	86
90°	0	

TEST NUMBER: P1504727

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-WHGL-PS (4000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8679.8
2.5°	8639.3
5°	8588.6
7.5°	8458.5
10°	8247.3
12.5°	8013.2
15°	7740.4
17.5°	7412.6
20°	7038.3
22.5°	6626.9
25°	6168.1
27.5°	5652.8
30°	5108.7
32.5°	4568.0
35°	4043.4
37.5°	3585.5
40°	3181.6
42.5°	2822.6
45°	2533.7
47.5°	2461.8
50°	2108.7
52.5°	1666.9
55°	1160.0
57.5°	720.6
60°	568.6
62.5°	446.9
65°	348.1
67.5°	283.0
70°	244.2
72.5°	220.5
75°	204.4
77.5°	183.3
80°	154.6
82.5°	119.1
85°	80.3
87.5°	39.7
90°	0.0

(END OF REPORT)