

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504906

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (4000K\_L12\_Medium\_120V)

Issue Date: 7/31/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1504906  
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/31/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (4000K\_L12\_Medium\_120V)  
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC WHITE SHADE, MEDIUM DISTRIBUTION  
LIGHT LEVEL 1 - 12,000 LUMENS  
Light Source:  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12099.1 lumens  
Efficiency: N/A  
Efficacy: 149.9 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.09  
Luminous Opening: Circular (Dia: 1.3' x H: 0')  
CIE Type: Direct

Input Watts (W): 80.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1504906

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (4000K\_L12\_Medium\_120V)

### Luminous Intensity Polar Plot





TEST NUMBER: P1504906

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (4000K\_L12\_Medium\_120V)

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |
| 1   | 111 | 108 | 104 | 101 | 109 | 106 | 103 | 100 | 101 | 99  | 97  | 98  | 96  | 94  | 94  | 93  | 91  | 89  |  |  |
| 2   | 104 | 98  | 92  | 88  | 102 | 96  | 91  | 87  | 92  | 88  | 85  | 89  | 86  | 83  | 86  | 84  | 81  | 79  |  |  |
| 3   | 97  | 89  | 82  | 77  | 95  | 87  | 81  | 77  | 85  | 80  | 75  | 82  | 78  | 74  | 80  | 76  | 73  | 71  |  |  |
| 4   | 91  | 81  | 74  | 69  | 89  | 80  | 73  | 68  | 78  | 72  | 68  | 75  | 71  | 67  | 73  | 69  | 66  | 64  |  |  |
| 5   | 85  | 75  | 67  | 62  | 83  | 73  | 67  | 62  | 72  | 66  | 61  | 70  | 65  | 60  | 68  | 63  | 60  | 58  |  |  |
| 6   | 80  | 69  | 61  | 56  | 78  | 68  | 61  | 56  | 66  | 60  | 55  | 65  | 59  | 55  | 63  | 58  | 55  | 53  |  |  |
| 7   | 75  | 64  | 56  | 51  | 73  | 63  | 56  | 51  | 61  | 55  | 51  | 60  | 55  | 50  | 59  | 54  | 50  | 48  |  |  |
| 8   | 70  | 59  | 52  | 47  | 69  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 50  | 46  | 55  | 50  | 46  | 44  |  |  |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 51  | 46  | 43  | 41  |  |  |
| 10  | 63  | 51  | 44  | 40  | 62  | 51  | 44  | 40  | 50  | 44  | 40  | 49  | 44  | 40  | 48  | 43  | 39  | 38  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    |
|-----|-------|
| 0°  | 63647 |
| 5°  | 63801 |
| 10° | 63732 |
| 15° | 63204 |
| 20° | 61564 |
| 25° | 59545 |
| 30° | 56192 |
| 35° | 46385 |
| 40° | 34540 |
| 45° | 23051 |
| 50° | 14027 |
| 55° | 10988 |
| 60° | 9250  |
| 65° | 9711  |
| 70° | 10596 |
| 75° | 11039 |
| 80° | 11124 |
| 85° | 10765 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $0^\circ$ 

Vertical Angle:  $45^\circ$

Luminance: 23051 cd/sqm

TEST NUMBER: P1504906

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (4000K\_L12\_Medium\_120V)

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 745.0   | 6.2       |
| 10°-20°   | 2115.1  | 17.5      |
| 20°-30°   | 3049.4  | 25.2      |
| 30°-40°   | 2898.6  | 24.0      |
| 40°-50°   | 1581.7  | 13.1      |
| 50°-60°   | 710.6   | 5.9       |
| 60°-70°   | 502.8   | 4.2       |
| 70°-80°   | 368.0   | 3.0       |
| 80°-90°   | 127.8   | 1.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-30°    | 5909.5  | 48.8      |
| 0°-40°    | 8808.1  | 72.8      |
| 0°-60°    | 11100.5 | 91.7      |
| 0°-90°    | 12099.1 | 100.0     |
| 90°-120°  | 0.0     | 0.0       |
| 90°-150°  | 0.0     | 0.0       |
| 90°-180°  | 0.0     | 0.0       |
| 0°-180°   | 12099.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 7848 |      |
| 5°  | 7838 | 745  |
| 15° | 7528 | 2115 |
| 25° | 6655 | 3049 |
| 35° | 4685 | 2899 |
| 45° | 2010 | 1582 |
| 55° | 777  | 711  |
| 65° | 506  | 503  |
| 75° | 352  | 368  |
| 85° | 116  | 128  |
| 90° | 0    |      |

TEST NUMBER: P1504906

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-WHGL-PS (4000K\_L12\_Medium\_120V)

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 7848.5 |
| 2.5°  | 7830.8 |
| 5°    | 7837.5 |
| 7.5°  | 7809.6 |
| 10°   | 7739.5 |
| 12.5° | 7654.2 |
| 15°   | 7528.3 |
| 17.5° | 7350.9 |
| 20°   | 7133.8 |
| 22.5° | 6902.3 |
| 25°   | 6654.7 |
| 27.5° | 6358.2 |
| 30°   | 6000.8 |
| 32.5° | 5385.8 |
| 35°   | 4685.4 |
| 37.5° | 3969.9 |
| 40°   | 3262.7 |
| 42.5° | 2620.7 |
| 45°   | 2009.9 |
| 47.5° | 1472.5 |
| 50°   | 1111.8 |
| 52.5° | 916.6  |
| 55°   | 777.2  |
| 57.5° | 653.9  |
| 60°   | 570.3  |
| 62.5° | 533.9  |
| 65°   | 506.1  |
| 67.5° | 480.7  |
| 70°   | 446.9  |
| 72.5° | 402.1  |
| 75°   | 352.3  |
| 77.5° | 297.4  |
| 80°   | 238.2  |
| 82.5° | 178.3  |
| 85°   | 115.7  |
| 87.5° | 56.6   |
| 90°   | 0.0    |

(END OF REPORT)