

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1221193

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)

Issue Date: 1/21/2026

Test Information

Test Method: LM-79-2019
Report Number: P1221193
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-574-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/21/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)
Description: PrentaLux UHBS2 SELECTABLE HIGH BAY. 1218 LIGHT ENGINE, BLACK SHADE, MEDIUM DISTRIBUTION.
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8802.3 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.02
Luminous Opening: Vertical Cylinder (Dia: 1.58' x H: 0.67')
CIE Type: Direct

Input Watts (W): 80.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1221193

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1221193

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74
5	91	82	76	71	89	81	75	71	79	74	70	77	73	69	76	72	69
6	86	76	70	65	84	75	69	65	74	69	65	72	68	64	71	67	64
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51
10	69	59	53	48	68	58	52	48	57	52	48	57	52	48	56	51	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40178
5°	38476
10°	36855
15°	35345
20°	33038
25°	30494
30°	26433
35°	18365
40°	10311
45°	3995
50°	1860
55°	360
60°	141
65°	128
70°	122
75°	108
80°	86
85°	53

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3995 cd/sqm

TEST NUMBER: P1221193

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	698.2	7.9
10°-20°	2004.5	22.8
20°-30°	2881.5	32.7
30°-40°	2334.7	26.5
40°-50°	725.2	8.2
50°-60°	105.8	1.2
60°-70°	21.3	0.2
70°-80°	16.1	0.2
80°-90°	6.5	0.1
90°-100°	0.1	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.5	0.0
130°-140°	1.2	0.0
140°-150°	2.1	0.0
150°-160°	2.3	0.0
160°-170°	1.8	0.0
170°-180°	0.7	0.0
0°-30°	5584.3	63.4
0°-40°	7918.9	90.0
0°-60°	8750.0	99.4
0°-90°	8793.9	99.9
90°-120°	0.1	0.0
90°-150°	3.9	0.0
90°-180°	9.0	0.1
0°-180°	8802.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7350	
5°	7340	698
15°	7142	2005
25°	6319	2882
35°	3785	2335
45°	794	725
55°	67	106
65°	21	21
75°	15	16
85°	6	6
90°	1	1
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	2	1
145°	3	2
155°	5	2
165°	6	2
175°	8	1
180°	8	

TEST NUMBER: P1221193

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7349.5
2.5°	7335.0
5°	7340.1
7.5°	7315.4
10°	7266.7
12.5°	7223.2
15°	7142.1
17.5°	6990.1
20°	6787.0
22.5°	6568.5
25°	6319.2
27.5°	6021.3
30°	5483.5
32.5°	4691.4
35°	3784.9
37.5°	2872.4
40°	2094.7
42.5°	1397.3
45°	793.8
47.5°	427.7
50°	358.5
52.5°	191.2
55°	66.6
57.5°	35.0
60°	24.8
62.5°	22.2
65°	21.3
67.5°	20.5
70°	18.8
72.5°	17.1
75°	15.4
77.5°	13.7
80°	11.1
82.5°	8.5
85°	6.0
87.5°	3.4
90°	0.9
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P1221193

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.9
130°	0.9
132.5°	0.9
135°	1.7
137.5°	1.7
140°	2.6
142.5°	2.6
145°	3.4
147.5°	4.3
150°	4.3
152.5°	4.3
155°	5.1
157.5°	5.1
160°	6.0
162.5°	6.0
165°	6.0
167.5°	6.8
170°	6.8
172.5°	6.8
175°	7.7
177.5°	7.7
180°	7.7

TEST NUMBER: P1221193

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-BLAK-08 (5000K_L12_Medium_120V)

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT