

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504241

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (5000K_L12_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504241
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (5000K_L12_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10842.2 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.98
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 81.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504241

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (5000K_L12_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504241

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (5000K_L12_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75		
4	93	84	77	73	91	83	77	72	81	75	71	78	74	70	76	73	69	68		
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62		
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47		
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44		
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78383
5°	77706
10°	75240
15°	71718
20°	66668
25°	59949
30°	51384
35°	42398
40°	35062
45°	29745
50°	26416
55°	14077
60°	5803
65°	2412
70°	636
75°	240
80°	316
85°	356

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 29958 cd/sqm

TEST NUMBER: P1504241

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (5000K_L12_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	797.6	7.4
10°-20°	2121.4	19.6
20°-30°	2712.7	25.0
30°-40°	2391.5	22.1
40°-50°	1828.8	16.9
50°-60°	844.6	7.8
60°-70°	132.2	1.2
70°-80°	10.0	0.1
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5631.7	51.9
0°-40°	8023.2	74.0
0°-60°	10696.6	98.7
0°-90°	10842.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10842.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8582	
5°	8476	798
15°	7585	2121
25°	5949	2713
35°	3803	2392
45°	2303	1829
55°	884	845
65°	112	132
75°	7	10
85°	3	3
90°	0	

TEST NUMBER: P1504241

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-BLAK-PS (5000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8582.5
2.5°	8539.9
5°	8476.0
7.5°	8335.5
10°	8113.2
12.5°	7867.1
15°	7585.1
17.5°	7250.4
20°	6859.5
22.5°	6432.0
25°	5949.1
27.5°	5428.7
30°	4872.5
32.5°	4322.3
35°	3802.8
37.5°	3347.1
40°	2940.9
42.5°	2578.1
45°	2303.0
47.5°	2216.1
50°	1859.2
52.5°	1399.3
55°	884.1
57.5°	458.2
60°	317.7
62.5°	202.7
65°	111.6
67.5°	55.4
70°	23.8
72.5°	9.4
75°	6.8
77.5°	6.8
80°	6.0
82.5°	4.3
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)