

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504608

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504608
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16270.8 lumens
Efficiency: N/A
Efficacy: 135.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.29
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 120.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504608

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504608

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	99	94	90	103	98	93	89	94	91	87	91	88	85	88	86	84	82		
3	98	90	84	80	96	89	83	79	86	81	78	84	80	76	81	78	75	73		
4	92	82	76	71	90	81	75	70	79	74	69	77	72	68	75	71	68	66		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	60	56	65	60	55	64	59	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77379
5°	77571
10°	77741
15°	78177
20°	78010
25°	78002
30°	77969
35°	77572
40°	71246
45°	55462
50°	34843
55°	17346
60°	3959
65°	1790
70°	726
75°	522
80°	598
85°	715

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 55462 cd/sqm

TEST NUMBER: P1504608

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	849.6	5.2
10°-20°	2460.0	15.1
20°-30°	3765.7	23.1
30°-40°	4538.9	27.9
40°-50°	3441.0	21.1
50°-60°	1090.8	6.7
60°-70°	99.3	0.6
70°-80°	18.0	0.1
80°-90°	7.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7075.2	43.5
0°-40°	11614.1	71.4
0°-60°	16145.9	99.2
0°-90°	16270.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16270.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8940	
5°	8928	850
15°	8724	2460
25°	8168	3766
35°	7341	4539
45°	4531	3441
55°	1150	1091
65°	87	99
75°	16	18
85°	7	8
90°	0	

TEST NUMBER: P1504608

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Wide_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	8939.9
2.5°	8922.0
5°	8928.0
7.5°	8902.8
10°	8845.3
12.5°	8790.3
15°	8724.4
17.5°	8615.4
20°	8469.3
22.5°	8317.3
25°	8167.6
27.5°	7998.8
30°	7801.2
32.5°	7586.8
35°	7341.4
37.5°	7024.1
40°	6305.6
42.5°	5466.2
45°	4531.0
47.5°	3534.8
50°	2587.6
52.5°	1803.3
55°	1149.5
57.5°	593.9
60°	228.7
62.5°	143.7
65°	87.4
67.5°	45.5
70°	28.7
72.5°	18.0
75°	15.6
77.5°	14.4
80°	12.0
82.5°	10.8
85°	7.2
87.5°	3.6
90°	0.0

(END OF REPORT)