

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504683

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-TRWH-PS (4000K_L12_Wide_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504683
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-TRWH-PS (4000K_L12_Wide_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC
TRANSLUCENT WHITE SHADE, WIDE DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13248.7 lumens
Efficiency: N/A
Efficacy: 164.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.31 / 1.3
Luminous Opening: Ellipsoidal Spheroid (W: 1.26' x L: 1.26' x H: 0.58')
CIE Type: Direct

Input Watts (W): 80.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504683

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-TRWH-PS (4000K_L12_Wide_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504683

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-TRWH-PS (4000K_L12_Wide_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	100	100	100	98		
1	111	107	104	101	108	105	102	99	100	98	95	96	94	92	92	91	89	87		
2	103	97	91	87	100	95	90	86	91	87	83	87	84	81	84	81	79	77		
3	96	87	81	76	93	86	80	75	83	77	73	80	75	72	77	73	70	68		
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	66	63	61		
5	83	72	65	59	81	71	64	59	69	63	58	67	61	57	65	60	56	54		
6	77	66	58	53	75	65	58	52	63	57	52	61	56	51	60	55	51	49		
7	72	60	53	47	70	60	52	47	58	51	47	56	51	46	55	50	46	44		
8	68	56	48	43	66	55	48	43	53	47	42	52	46	42	51	46	42	40		
9	63	51	44	39	62	51	44	39	49	43	39	48	42	38	47	42	38	36		
10	60	48	40	36	58	47	40	36	46	40	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):



MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: -
Vertical Angle: -
Luminance: -

TEST NUMBER: P1504683

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-TRWH-PS (4000K_L12_Wide_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	622.0	4.7
10°-20°	1802.7	13.6
20°-30°	2773.4	20.9
30°-40°	3370.2	25.4
40°-50°	2634.0	19.9
50°-60°	1021.3	7.7
60°-70°	332.8	2.5
70°-80°	256.1	1.9
80°-90°	142.7	1.1
90°-100°	52.7	0.4
100°-110°	52.6	0.4
110°-120°	49.3	0.4
120°-130°	43.7	0.3
130°-140°	36.3	0.3
140°-150°	28.1	0.2
150°-160°	18.8	0.1
160°-170°	9.4	0.1
170°-180°	2.6	0.0
0°-30°	5198.1	39.2
0°-40°	8568.3	64.7
0°-60°	12223.6	92.3
0°-90°	12955.2	97.8
90°-120°	154.6	1.2
90°-150°	262.7	2.0
90°-180°	293.0	2.2
0°-180°	13248.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6544	
5°	6536	622
15°	6390	1803
25°	6013	2773
35°	5450	3370
45°	3460	2634
55°	1094	1021
65°	327	333
75°	245	256
85°	134	124
90°	48	32
95°	48	40
105°	50	53
115°	50	49
125°	49	44
135°	46	36
145°	45	28
155°	41	19
165°	33	9
175°	26	3
180°	26	

TEST NUMBER: P1504683

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-TRWH-PS (4000K_L12_Wide_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	6544.1
2.5°	6530.6
5°	6535.6
7.5°	6519.6
10°	6474.8
12.5°	6438.5
15°	6390.3
17.5°	6315.1
20°	6216.3
22.5°	6114.9
25°	6012.7
27.5°	5900.3
30°	5766.0
32.5°	5617.3
35°	5450.0
37.5°	5223.6
40°	4717.5
42.5°	4116.9
45°	3459.6
47.5°	2765.1
50°	2097.7
52.5°	1552.8
55°	1094.1
57.5°	703.7
60°	436.8
62.5°	373.4
65°	327.0
67.5°	290.6
70°	272.0
72.5°	256.8
75°	245.0
77.5°	228.9
80°	205.3
82.5°	174.0
85°	134.3
87.5°	88.7
90°	48.2
92.5°	47.3
95°	48.2
97.5°	49.0
100°	49.0
102.5°	49.8
105°	49.8
107.5°	49.8
110°	49.8

TEST NUMBER: P1504683

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-TRWH-PS (4000K_L12_Wide_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	49.8
115°	49.8
117.5°	49.8
120°	49.0
122.5°	49.0
125°	49.0
127.5°	48.2
130°	48.2
132.5°	47.3
135°	46.5
137.5°	46.5
140°	45.6
142.5°	45.6
145°	44.8
147.5°	43.9
150°	43.9
152.5°	42.2
155°	40.6
157.5°	38.0
160°	37.2
162.5°	34.6
165°	32.9
167.5°	31.3
170°	28.7
172.5°	27.0
175°	26.2
177.5°	26.2
180°	26.2

(END OF REPORT)