

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504861

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-TRWH-PS (4000K_L12_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504861
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-62)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-TRWH-PS (4000K_L12_Medium_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC
TRANSLUCENT WHITE SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11634.1 lumens
Efficiency: N/A
Efficacy: 144.2 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.07
Luminous Opening: Ellipsoidal Spheroid (W: 1.3' x L: 1.3' x H: 0.75')
CIE Type: Direct

Input Watts (W): 80.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504861

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-TRWH-PS (4000K_L12_Medium_120V)

Luminous Intensity Polar Plot






TEST NUMBER: P1504861

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-TRWH-PS (4000K_L12_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	118	118	118	118	115	115	115	115	109	109	109	103	103	103	98	98	98	98	98	98	98	98			
1	110	107	103	100	107	104	101	98	99	97	95	95	93	91	91	89	88	88	88	88	88	86			
2	103	97	92	87	100	95	90	86	91	87	83	87	84	81	83	81	79	79	79	79	79	76			
3	96	88	82	77	94	86	81	76	83	78	74	80	76	72	77	74	71	71	71	71	71	69			
4	90	81	74	68	88	79	73	68	76	71	66	74	69	65	71	67	64	64	64	64	64	62			
5	84	74	67	62	82	73	66	61	70	65	60	68	63	59	66	62	58	58	58	58	58	56			
6	79	68	61	56	77	67	60	55	65	59	55	63	58	54	61	57	53	53	53	53	53	51			
7	74	63	56	51	73	62	55	51	61	54	50	59	53	49	57	53	49	49	49	49	49	47			
8	70	59	52	47	68	58	51	46	56	50	46	55	49	46	54	49	45	45	45	45	45	43			
9	66	55	48	43	65	54	47	43	53	47	42	51	46	42	50	45	42	42	42	42	42	40			
10	62	51	44	40	61	50	44	40	49	43	39	48	43	39	47	42	39	39	39	39	39	37			

AVERAGE LUMINANCE (cd/sqm):



MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: -
Vertical Angle: -
Luminance: -

TEST NUMBER: P1504861

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-TRWH-PS (4000K_L12_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	718.4	6.2
10°-20°	2018.6	17.4
20°-30°	2867.5	24.6
30°-40°	2670.8	23.0
40°-50°	1419.0	12.2
50°-60°	593.6	5.1
60°-70°	398.6	3.4
70°-80°	314.5	2.7
80°-90°	161.6	1.4
90°-100°	85.6	0.7
100°-110°	85.6	0.7
110°-120°	80.1	0.7
120°-130°	70.5	0.6
130°-140°	57.7	0.5
140°-150°	43.9	0.4
150°-160°	29.2	0.3
160°-170°	14.9	0.1
170°-180°	4.0	0.0
0°-30°	5604.4	48.2
0°-40°	8275.2	71.1
0°-60°	10287.8	88.4
0°-90°	11162.5	95.9
90°-120°	251.3	2.2
90°-150°	423.5	3.6
90°-180°	472.0	4.1
0°-180°	11634.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7586	
5°	7568	718
15°	7193	2019
25°	6261	2867
35°	4305	2671
45°	1800	1419
55°	647	594
65°	398	399
75°	300	315
85°	147	136
90°	78	47
95°	79	64
105°	81	86
115°	81	80
125°	79	71
135°	74	58
145°	70	44
155°	63	29
165°	52	15
175°	40	4
180°	40	

TEST NUMBER: P1504861

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-TRWH-PS (4000K_L12_Medium_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	7585.5
2.5°	7567.7
5°	7568.5
7.5°	7526.4
10°	7442.2
12.5°	7338.5
15°	7192.8
17.5°	6992.8
20°	6757.1
22.5°	6519.0
25°	6260.7
27.5°	5959.4
30°	5593.4
32.5°	4990.9
35°	4305.0
37.5°	3629.6
40°	2981.7
42.5°	2381.7
45°	1800.2
47.5°	1285.2
50°	970.2
52.5°	783.1
55°	647.0
57.5°	525.6
60°	451.1
62.5°	419.5
65°	398.4
67.5°	383.9
70°	362.0
72.5°	333.6
75°	299.6
77.5°	264.0
80°	225.9
82.5°	185.4
85°	146.6
87.5°	109.3
90°	77.7
92.5°	76.9
95°	78.6
97.5°	79.4
100°	80.2
102.5°	81.0
105°	81.0
107.5°	81.0
110°	81.0

TEST NUMBER: P1504861

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-TRWH-PS (4000K_L12_Medium_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	81.0
115°	81.0
117.5°	80.2
120°	80.2
122.5°	79.4
125°	78.6
127.5°	77.7
130°	76.9
132.5°	75.3
135°	74.5
137.5°	73.7
140°	72.1
142.5°	71.3
145°	69.6
147.5°	68.8
150°	67.2
152.5°	65.6
155°	63.2
157.5°	59.9
160°	58.3
162.5°	55.1
165°	51.8
167.5°	48.6
170°	45.3
172.5°	42.1
175°	40.5
177.5°	41.3
180°	40.5

(END OF REPORT)