

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504367

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (4000K_L12_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504367
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (4000K_L12_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE
SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12009.2 lumens
Efficiency: N/A
Efficacy: 148.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 80.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504367

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (4000K_L12_Narrow_120V)

Luminous Intensity Polar Plot



TEST NUMBER: P1504367

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (4000K_L12_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41		
10	63	51	44	40	61	51	44	40	50	44	40	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78956
5°	78390
10°	76115
15°	72898
20°	68184
25°	61884
30°	53635
35°	44958
40°	37700
45°	32441
50°	29589
55°	17690
60°	10123
65°	7339
70°	6406
75°	7244
80°	8489
85°	9295

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 32892 cd/sqm

TEST NUMBER: P1504367

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (4000K_L12_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	805.3	6.7
10°-20°	2157.3	18.0
20°-30°	2799.3	23.3
30°-40°	2532.3	21.1
40°-50°	1997.2	16.6
50°-60°	1052.4	8.8
60°-70°	357.5	3.0
70°-80°	214.6	1.8
80°-90°	93.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5761.9	48.0
0°-40°	8294.2	69.1
0°-60°	11343.9	94.5
0°-90°	12009.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12009.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8645	
5°	8551	805
15°	7710	2157
25°	6141	2799
35°	4032	2532
45°	2512	1997
55°	1111	1052
65°	340	358
75°	205	215
85°	89	93
90°	0	

TEST NUMBER: P1504367

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (4000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8645.2
2.5°	8603.8
5°	8550.6
7.5°	8420.5
10°	8207.6
12.5°	7976.1
15°	7709.9
17.5°	7385.5
20°	7015.5
22.5°	6600.7
25°	6141.1
27.5°	5625.7
30°	5085.9
32.5°	4550.3
35°	4032.4
37.5°	3568.6
40°	3162.2
42.5°	2799.8
45°	2511.7
47.5°	2433.1
50°	2082.5
52.5°	1629.7
55°	1111.0
57.5°	697.0
60°	554.2
62.5°	435.1
65°	339.6
67.5°	277.1
70°	239.9
72.5°	218.8
75°	205.3
77.5°	187.6
80°	161.4
82.5°	128.4
85°	88.7
87.5°	44.8
90°	0.0

(END OF REPORT)