

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504376

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (5000K_L12_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504376
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (5000K_L12_Narrow_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, DOMIC WHITE
SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12106.7 lumens
Efficiency: N/A
Efficacy: 149.3 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1
Luminous Opening: Circular (Dia: 1.23' x H: 0')
CIE Type: Direct

Input Watts (W): 81.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504376

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (5000K_L12_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504376

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (5000K_L12_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	55	53		
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41		
10	63	51	44	40	61	51	44	40	50	44	40	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79596
5°	79025
10°	76733
15°	73489
20°	68737
25°	62386
30°	54070
35°	45323
40°	38007
45°	32704
50°	29829
55°	17833
60°	10205
65°	7399
70°	6459
75°	7304
80°	8557
85°	9368

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 33159 cd/sqm

TEST NUMBER: P1504376

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (5000K_L12_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	811.8	6.7
10°-20°	2174.8	18.0
20°-30°	2822.1	23.3
30°-40°	2552.8	21.1
40°-50°	2013.4	16.6
50°-60°	1061.0	8.8
60°-70°	360.5	3.0
70°-80°	216.3	1.8
80°-90°	94.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5808.7	48.0
0°-40°	8361.5	69.1
0°-60°	11435.9	94.5
0°-90°	12106.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12106.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8715	
5°	8620	812
15°	7772	2175
25°	6191	2822
35°	4065	2553
45°	2532	2013
55°	1120	1061
65°	342	360
75°	207	216
85°	89	94
90°	0	

TEST NUMBER: P1504376

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-A-04-WHGL-PS (5000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	8715.3
2.5°	8673.6
5°	8619.9
7.5°	8488.8
10°	8274.2
12.5°	8040.8
15°	7772.5
17.5°	7445.5
20°	7072.4
22.5°	6654.2
25°	6190.9
27.5°	5671.4
30°	5127.2
32.5°	4587.2
35°	4065.1
37.5°	3597.5
40°	3187.9
42.5°	2822.5
45°	2532.1
47.5°	2452.9
50°	2099.4
52.5°	1642.9
55°	1120.0
57.5°	702.6
60°	558.7
62.5°	438.6
65°	342.4
67.5°	279.4
70°	241.9
72.5°	220.6
75°	207.0
77.5°	189.1
80°	162.7
82.5°	129.5
85°	89.4
87.5°	45.1
90°	0.0

(END OF REPORT)