

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504606

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Medium_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504606
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-29)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Medium_120V)
Description: PrentaLux UHBS2 4-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, MEDIUM DISTRIBUTION
LIGHT LEVEL 1 - 18,000 LUMENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15910.5 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.12
Luminous Opening: Circular (Dia: 1.26' x H: 0')
CIE Type: Direct

Input Watts (W): 120.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504606

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Medium_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504606

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Medium_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91							
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83							
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74							
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67							
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61							
6	81	71	64	59	80	70	63	58	68	62	58	67	61	57	65	61	57	55							
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50							
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46							
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43							
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91744
5°	91855
10°	91433
15°	90410
20°	87473
25°	83628
30°	77693
35°	68601
40°	55810
45°	43254
50°	34134
55°	17509
60°	6114
65°	2648
70°	787
75°	401
80°	419
85°	477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43254 cd/sqm

TEST NUMBER: P1504606

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Medium_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1003.9	6.3
10°-20°	2831.5	17.8
20°-30°	4009.8	25.2
30°-40°	4012.0	25.2
40°-50°	2775.4	17.4
50°-60°	1108.6	7.0
60°-70°	149.3	0.9
70°-80°	15.0	0.1
80°-90°	5.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7845.2	49.3
0°-40°	11857.2	74.5
0°-60°	15741.2	98.9
0°-90°	15910.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15910.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10600	
5°	10572	###
15°	10090	2832
25°	8757	4010
35°	6492	4012
45°	3534	2775
55°	1160	1109
65°	129	149
75°	12	15
85°	5	5
90°	0	

TEST NUMBER: P1504606

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-04-BLAK-PS (5000K_L18_Medium_120V)

CANDELA DISTRIBUTION (FULL):

	0°
0°	10599.6
2.5°	10575.6
5°	10572.0
7.5°	10519.3
10°	10403.2
12.5°	10270.3
15°	10089.5
17.5°	9828.4
20°	9496.7
22.5°	9143.5
25°	8756.7
27.5°	8314.9
30°	7773.6
32.5°	7164.2
35°	6492.4
37.5°	5753.6
40°	4939.4
42.5°	4198.2
45°	3533.6
47.5°	2997.1
50°	2534.9
52.5°	1884.7
55°	1160.3
57.5°	544.8
60°	353.2
62.5°	225.1
65°	129.3
67.5°	63.5
70°	31.1
72.5°	14.4
75°	12.0
77.5°	10.8
80°	8.4
82.5°	7.2
85°	4.8
87.5°	2.4
90°	0.0

(END OF REPORT)