

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504781

Luminaire Tested: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Narrow_120V)

Issue Date: 7/31/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504781
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2602-677-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/31/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Narrow_120V)
Description: PrentaLux UHBS2 6-INCH SELECTABLE HIGH BAY 1218 LIGHT ENGINE, CONIC BLACK SHADE, NARROW DISTRIBUTION
LIGHT LEVEL 1 - 12,000 LUMENS
Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9409.5 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.96
Luminous Opening: Circular (Dia: 1.3' x H: 0')
CIE Type: Direct

Input Watts (W): 81.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504781

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Narrow_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P1504781

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Narrow_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93								
2	107	102	97	93	105	100	96	92	97	93	90	93	91	88	91	89	87	85								
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78								
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71								
5	90	80	74	69	88	79	74	69	78	72	68	76	71	68	74	70	67	66								
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60								
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56								
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52								
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48								
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69005
5°	68465
10°	66374
15°	63266
20°	58815
25°	53033
30°	45387
35°	35514
40°	27049
45°	17660
50°	9144
55°	4575
60°	1064
65°	376
70°	363
75°	373
80°	360
85°	400

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17660 cd/sqm

TEST NUMBER: P1504781

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Narrow_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	791.5	8.4
10°-20°	2107.3	22.4
20°-30°	2699.2	28.7
30°-40°	2254.6	24.0
40°-50°	1205.1	12.8
50°-60°	308.1	3.3
60°-70°	26.9	0.3
70°-80°	12.2	0.1
80°-90°	4.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5598.0	59.5
0°-40°	7852.7	83.5
0°-60°	9365.8	99.5
0°-90°	9409.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9409.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8509	
5°	8410	792
15°	7536	2107
25°	5927	2699
35°	3587	2255
45°	1540	1205
55°	324	308
65°	20	27
75°	12	12
85°	4	5
90°	0	

TEST NUMBER: P1504781

CATALOG NUMBER: PRLX-UHBS2-1218-MV-L8C5-U-B-06-BLAK-PS (5000K_L12_Narrow_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	8509.2
2.5°	8462.4
5°	8410.4
7.5°	8273.3
10°	8060.4
12.5°	7821.1
15°	7535.7
17.5°	7195.1
20°	6815.2
22.5°	6395.3
25°	5926.9
27.5°	5404.0
30°	4847.0
32.5°	4192.9
35°	3587.3
37.5°	3053.3
40°	2555.1
42.5°	2033.0
45°	1539.9
47.5°	1111.5
50°	724.8
52.5°	524.6
55°	323.6
57.5°	156.7
60°	65.6
62.5°	32.4
65°	19.6
67.5°	17.0
70°	15.3
72.5°	13.6
75°	11.9
77.5°	9.4
80°	7.7
82.5°	6.0
85°	4.3
87.5°	2.6
90°	0.0

(END OF REPORT)